Opto Plus LED Corp.
0.56” SMD Type LED Display
OPS-S5620SE | OPS-S5621SE

EDIT HISTORY

Version A: Dec. 01, 2020

Preliminary Spec.

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

www.opledtw.com

Opto Plus LED Corp.
0.56” SMD Type LED Display
OPS-S5620SE | OPS-S5621SE

FEATURES

- 0.56 inch (14.20 mm) digit height.
- SMD type.
- Low current operation.
- RoHS Compliant, Pb Free.

DESCRIPTION

The device are 0.56 inch (14.20 mm) height single digit 7-segment displays.

The device is Opto Plus LED Corp standard LED Display.

This device utilizes Super Bright Red LED chip which are made from AlGaInP

On a transparent GaAs, substrate.

The device has face and segment option, please refer to **PRODUCT APPEARANCE**.

DEVICE

PART NO.		DESCRIPTION
	OPS-S5620SE-GW	Common Anode | Gray face | White segment
	OPS-S5621SE-GW	Common Cathode | Gray face | White segment
	OPS-S5620SE-BW	Common Anode | Black face | White segment
	OPS-S5621SE-BW	Common Cathode | Black face | White segment

RoHS Compliance


Pb Free.

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

Opto Plus LED Corp.
0.56” SMD Type LED Display
OPS-S5620SE | OPS-S5621SE

MECHANICAL DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are± 0.25 mm unless otherwise noted.


Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice


Opto Plus LED Corp.
0.56” SMD Type LED Display
OPS-S5620SE | OPS-S5621SE


● TYPICAL INTERNAL EQUIVALENT CIRCUIT

Recommended Soldering Pattern




Turn On Color





OPS-S5620
(Common Anode)



OPS-S5621
(Common Cathode)



※EMITTED COLOR：SUPER BRIGHT RED

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

PRODUCT APPEARANCE

The most common reflector color and segment color are show in below diagram.

-GW	-BW
	
※ REFLECTOR COLOR: Gray ※ SEGMENT COLOR: White	※ REFLECTOR COLOR: Black ※ SEGMENT COLOR: White

Opto Plus can customize reflector and segment colors by customer’s request. If you have these request please visit www.opledtw.com or contact sales@opledtw.com for more **Standard Product Customization** information.

Part NO. related to reflector and segment colors show as table below.

PART NO.	DESCRIPTION
OPS-S5620SE-GW	Common Anode ｜ Gray face ｜ White segment
OPS-S5621SE-GW	Common Cathode ｜ Gray face ｜ White segment
OPS-S5620SE-BW	Common Anode ｜ Black face ｜ White segment
OPS-S5621SE-BW	Common Cathode ｜ Black face ｜ White segment

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

SE: SUPER BRIGHT RED (AlGaInP/GaAs)

ABSOLUTE MAXIMUM RATING AT Ta=25°C

Parameter	Symbol	Maximum Rating	Unit
Power dissipation	P_{AD}	48	mW
Continuous forward current	I_{AF}	20	mA
Peak current (duty cycle 1/10, 1kHz)	I_{PF}	40	mA
Reverse voltage	V_R	5	V
Operating temperature	T_{OPR}	-40 to +105	°C
Storage temperature	T_{STG}	-40 to +105	°C

ELECTRICAL - OPTICAL CHARACTERISTICS AT Ta=25°C

Characteristic	Symbol	Condition	Min.	Type.	Max.	Unit
Forward Voltage, (Per Dice)	V_F	I_F =20mA	-	2.1	2.4	V
Reverse Current, (Per Dice)	I_R	V_R =5V	-	-	10	μA
Peak Wavelength	λ_P	I_F =20mA	-	632	-	nm
Dominant Wavelength	λ_D	I_F =20mA	619	-	629	nm
Luminous Intensity	I_V	I_F =20mA	25	55	85	mcd
Spectral Line Half-Bandwidth	$\Delta\lambda$	I_F =20mA	-	20	-	nm

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

SE: BIN GRADE (Unit : mcd) 20mA

Super Bright Red	M	N	O
	25.0 - 45.0	45.1 - 65.0	65.1 - 85.0

SE: HUE GRADE (λ_D : nm)

1	2	3
619.0 – 622.0	622.1 – 626.0	626.1 – 629.0

AVAILABLE BIN / HUE TABLE

M1	N1	O1
M2	N2	O2
M3	N3	O3

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

SE: SUPER BRIGHT RED (AlGaInP/GaAs) CURVE

Typical Electro-optical Characteristic Curves
(25℃ Free Air Temperature Unless Otherwise Specified)




Fig.1—Relative Intensity VS. Wavelength




Fig.2—Relative Luminous Intensity vs. Forward Current




Fig.3—Forward Current vs. Forward Voltage




Fig.4—Relative Intensity(@20mA) vs. Ambient Temperature




Fig.5—Forward Voltage(@20mA) vs. Ambient Temperature




Fig.6—Dominant Wavelength(@20mA)
VS. Ambient Temperature




Fig.7—Max. Allowable DC Current
VS. Ambient Temperature


Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

SMT REFLOW SOLDERING INSTRUCTIONS

SMT Soldering Profile

Pb free reflow soldering Profile



- We recommend the reflow temperature 245°C (+/- 5°C).
  The maximum soldering temperature should be limited to 260°C.
- Number of reflow process shall be 2 times or less.

SOLDERING IRON

Basic spec is ≦4 sec when 260°C. If temperature is higher, time should Be shorter (+10°C→1 sec). Power dissipation of Iron should be smaller Than 15W, and temperature should be controllable. Surface temperature Of the device should be under 230°C.


REWORK

- Customer must finish rework within 3 sec. under 350℃.
- The head of soldering iron cannot touch copper foil.


Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice

REEL DIMENSIONS



PACKING & LABEL SPECIFICATIONS



STORAGED CONDITION

In factory original sealed bag package

TEMPERATURE CONDITION	HUMIDITY CONDITION
5℃ ~ 30℃	Below 60%RH

After opened and not in factory original sealed bag package

TEMPERATURE CONDITION	HUMDITY CONDITION	STORAGE TIME
5℃ ~ 30℃	Below 60%RH	Within 4 weeks (MSL as level 2a)

Opto Plus LED Corp. 7F-3, No.496 , Bannan Road, Jhonghe Dist., New Taipei City 235, Taiwan (R.O.C)
Website: www.opledtw.com E-mail: sales@opledtw.com Tel: 886-2-2222-5698 Fax: 886-2-2222-2566

Disclaimer:
Subject to change without notice