



BETA 1228RTX

Screwdrivers for Tamper Resistant Torx® screws, with handles



Certifications and Standards



Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the palm contact points, improving thrust and clamping efficiency.

CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

Dimensions



Certifications and Standards

Coded items

	Art.		L mm	L1 mm	Ø mm
012280109	1228RTX 9	T9	60	169	4
012280110	1228RTX 10	T10	80	189	4
012280115	1228RTX 15	T15	80	189	4
012280120	1228RTX 20	T20	100	209	4,5
012280125	1228RTX 25	T25	100	209	5
012280127	1228RTX 27	T27	115	236	6
012280130	1228RTX 30	T30	115	236	6
012280140	1228RTX 40	T40	130	263	7

Scan the QR Code to access the web tab
Specs, media and documentation in one click.

