


C4AQ, Film, Metallized Polypropylene, Automotive DC Link, 7.5 uF, 5%, 800 VDC, 70°C, Lead Spacing = 27.5mm



Dimensions

L	32mm +0.5/-0.7mm
H	19mm +0.2/-0.7mm
T	31mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Box
Packaging Quantity:	80

General Information

Series:	C4AQ
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200:	Yes
Miscellaneous:	Rth = 30 C/W.

Specifications

Capacitance:	7.5 uF
Capacitance Tolerance:	5%
Voltage DC:	800 VDC
Temperature Range:	-55/+105°C
Rated Temperature:	70°C
Dissipation Factor:	0.02% (10 kHz 25C)
Insulation Resistance:	4 MOhms
Max dV/dt:	19 V/us
Resistance:	7.3 mOhms (10kHz 70C)
Ripple Current:	7.7 Amps Irms (10kHz 70C), 145 Amps Ipk
Inductance:	16 nH