

WLAN 802.11 b/g/n Antenna N plug 5 dBi omnidirectional fixed outdoor white

Description

This Wireless LAN antenna by Delock can be connected to a WLAN device with N interface, in order to send and receive signals.



Item no. 88452

EAN: 4043619884520

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connector: N plug
- Frequency range: 2.4 GHz - 2.5 GHz
- Antenna gain: 3.0 dBi
- Impedance: 50 Ohm
- Polarisation: linear, vertical
- VSWR: 2.0
- Operating temperature: -40 °C ~ 70 °C
- Housing material: polycarbonate
- IP67 protection class
- Length: ca. 166.5 mm
- Diameter:
 - ca. 18.30 mm (top)
 - ca. 22.50 mm (N)
- Maximum Transmission power: 20 W
- Maximum wind speed: 216 km/h
- Splash proof

System requirements

- Device with a free N jack

Package content

- WLAN antenna

General

Protection class:	IP67
-------------------	------

Interface

Connector:	N plug
------------	--------

Technical characteristics

Frequency range:	2.4 - 2.5 GHz
Antenna gain:	3 dBi
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 70 °C
Polarisation:	linear vertical
Transmission power:	20 W
VSWR:	2.0

Physical characteristics

Housing material:	Polycarbonat
Length:	166.5 mm
Diameter connector:	22.50 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

