



### Polyester braided sleeving for reduction of vibration noise

#### Helagaine HEGSAS

Helagaine HEGSAS is used primarily in the automotive sector and wherever vibration noise must be reduced. Helagaine HEGSAS can be supplied in pre-cut lengths on request.

#### Features and Benefits

- Superior noise reduction
- Made of sturdy polyester
- Highly flexible
- Expansion rate of 3:1
- Easy to apply over irregular shapes due
- High surface coverage
- Excellent abrasion resistance



Helagaine HEGSAS braided sleeving.

|                              |                                         |
|------------------------------|-----------------------------------------|
| <b>MATERIAL</b>              | Polyester (PET)                         |
| <b>Operating Temperature</b> | -50 °C to +150 °C, intermittent +200 °C |
| <b>Melting Point</b>         | +250 °C                                 |
| <b>Flammability</b>          | FMVSS 302                               |

HF ✓

RoHS ✓



To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0. See page 533.

| TYPE     | Bundle<br>Ø min. | Bundle<br>Ø max. | Colour     | Reel<br>Length | Article-No. |
|----------|------------------|------------------|------------|----------------|-------------|
| HEGSAS04 | 2.0              | 8.0              | Black (BK) | 200 m          | 170-60401   |
| HEGSAS06 | 4.0              | 11.0             | Black (BK) | 200 m          | 170-60600   |
| HEGSAS09 | 6.0              | 16.0             | Black (BK) | 100 m          | 170-60900   |
| HEGSAS12 | 8.0              | 20.0             | Black (BK) | 100 m          | 170-61200   |
| HEGSAS15 | 10.0             | 24.0             | Black (BK) | 50 m           | 170-61500   |
| HEGSAS20 | 13.0             | 30.0             | Black (BK) | 50 m           | 170-62000   |
| HEGSAS30 | 20.0             | 40.0             | Black (BK) | 25 m           | 170-63000   |
| HEGSAS40 | 30.0             | 50.0             | Black (BK) | 25 m           | 170-64000   |

All dimensions in mm. Subject to technical changes.

Colour grey available on request. Cuts in any lengths. Minimum Order Quantity (MOQ) may differ from package content.