

Han Q 4/2 male insert with Quick Lock



Part number	09 12 006 2663
Specification	Han Q 4/2 male insert with Quick Lock
HARTING eCatalogue	https://b2b.harting.com/09120062663

Identification

Category	Inserts
Series	Han [®] Q
Identification	4/2

Version

Termination method	Axial screw termination
Gender	Male
Size	Han-Compact [®]
Number of contacts	4
Additional contacts	+ 2 additional signal contacts
PE contact	Yes
Details	With Han-Quick Lock [®] signal contacts

Technical characteristics

Conductor cross-section	4 ... 10 mm ² 0.25 ... 1.5 mm ² Signal
Rated current	40 A
Rated voltage conductor-earth	400 V
Rated voltage conductor-conductor	690 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current (signal)	10 A
Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV



Pushing Performance

Technical characteristics

Pollution degree (signal)	3
Insulation resistance	$>10^{10} \Omega$
Contact resistance	$\leq 0.3 \text{ m}\Omega$
Contact resistance, signal area	$< 3 \text{ m}\Omega$
Limiting temperature	-40 ... +125 °C
Tightening torque	1.8 Nm
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	45.54 g
Country of origin	Germany



Pushing Performance

Commercial data

European customs tariff number 85366990

eCl@ss 27440205 Contact insert for industrial connectors