


PRODUCT SPECIFICATION

Part Number	USB4731			Rev	A		Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin					Page	1	
Doc Number	USB Type C	Prepared	CC	Checked	YR	Approved	PH	



PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A		Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin				Page	2
Doc Number	USB Type C	Prepared	CC	Checked	YR	Approved PH

1.0 SCOPE

This specification covers performance, tests and quality requirements for the USB Type C Receptacle USB4731.

2.0 PRODUCT NAME AND PART NUMBER

USB Type C Receptacle USB4731.

3.0 PRODUCT SHAPE, DIMENSIONS AND MATERIAL

Please refer to drawing.

4.0 RATINGS

4.1 Current rating: 5.00A collectively for VBUS pins (i.e., pins A4, B4, A9, B9)

6.25A collectively for GND pins (i.e., pins A1, B1, A12, B12)

1.25A for VCONN (i.e., A5/B5)

0.25A per pin for all other pins

4.2 Voltage rating 48V DC

4.3 Power rating 240W

4.4 Operating Temperature Range ... -30°C to +85°C

5.0 TEST AND MEASUREMENT CONDITIONS

Product is designed to meet electrical, mechanical and environmental performance requirements specified below. All tests are performed in ambient conditions unless otherwise specified.

6.0 PERFORMANCE

Test No	Item	Test Condition	Requirement
6.0.1	Examination of Product	Visual, dimensional and functional inspection as per quality plan.	Product shall meet requirements of product drawing and specification.
	Reseating	Manually plug/unplug 3 times	No physical damage

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	3
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

6.1 Electrical Performance

Test No	Item	Test Condition	Requirement
6.1.1	Low Level Contact Resistance	The low-level contact resistance measurement is made from the solder tail of the receptacle to the soldering point of the plug. When measured at 20mV Max. open circuit at 100mA. Mated test contacts must be in a connector housing. In accordance with EIA-364-23, Test Condition B	40mΩ max. (initial)
6.1.2	Insulation Resistance	Both unmated and Mated connectors, apply 100V DC for 1 minute at sea level between adjacent terminal or ground. In accordance with EIA-364-21.	100 MΩ Min. (initial)
6.1.3	Dielectric Strength	Mate connectors, apply 100V AC (RMS) for 1 minute at sea level. In accordance with EIA-364-20.	No Breakdown
6.1.4	Contact current rating	A current of 5A shall be applied collectively to VBUS pins (i.e., pins A4, B4, A9, B9) and 1.25 A shall be applied to the VCONN pin (i.e., B5) as applicable, terminated through the corresponding GND pins (i.e., pins A1, B1, A12, B12). A minimum current of 0.25 A shall also be applied individually to all the other contacts, as applicable.	The temperature rise shall not exceed 30°C at the outside surface of the shell.

6.2 Mechanical Performance

Test No	Item	Test Condition	Requirement
6.2.1	Mating/Un-mating Force	Mate/Un-mated at a speed of 12.5mm/min. In accordance with EIA-364-13.	Mating force: within 5N to 20N (initial). Un-Mating force: within 8N to 20N up to 30 cycles, within 6N to 20N after 20,000 cycles
6.2.2	Durability	20,000 cycles at a cycle rate 500± 50per hour. In accordance with EIA-364-09. (Replace the plug after 10K cycles)	Un-Mating force: within 6N to 20N Contact resistance: 50mΩ max. Dielectric Strength: no breakdown
	Durability (Preconditioning)	50 cycles at a cycle rate 500± 50 per hour In accordance with EIA-364-09.	-

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	4
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

6.2.3	Vibration	EIA 364-28 Test Condition VII, Test Letter D 15 minutes in each of 3 mutually perpendicular directions. Both mating halves should be rigidly fixed so as not to contribute to the relative motion of one contact against another. The method of fixturing should be detailed in the test report.	No evidence of physical damage and no discontinuity longer than 1 microsecond. Contact resistance: 50mΩ max.
6.2.4	4-Axis Continuity	Shall be tested for continuity under stress using a test fixture	No evidence of physical damage and no discontinuity longer than 1 microsecond.

6.3 Environmental Performance and Others

Test No	Item	Test Condition	Requirement
6.3.1	Cyclic Temperature and Humidity Test	Cycle the connector between 25 °C ±3 °C at 80 % ±3% RH and 65 °C ±3 °C at 50 % ±3% RH. Ramp times should be 0.5 hour and dwell times should be 1.0 hour. Dwell times start when the temperature and humidity have stabilized within the specified levels. Perform 24 such cycles.	Contact Resistance: 50mΩ Max.
6.3.2	Salt Spray	Subject mated connectors to 5±1% salt-solution concentration, 35±2°C for 24 hours. In accordance with EIA-364-26, Test Condition B.	Shall meet visual requirements, no detrimental corrosion allowed in contact area and base metal exposed.
6.3.3	Thermal Shock	Temperature range from -55°C~+85°C. Start from -55°C. After 30 min. change to +85°C, change time is no more than 5min. Total 10 cycles. Test reference standard: EIA 364-32, test condition I	No physical damage. Contact Resistance (Low Level) 50mΩ Max.
6.3.4	Solderability	Solder pot temperature: 250±5°C for 3~5 seconds. In accordance with EIA-364-52.	95% of immersed area must show no voids, pin holes.
6.3.5	Temperature life	105° C without applied voltage for 120 hours. EIA-364-17, method A	Contact resistance: 50mΩ max.
	Temperature Life (preconditioning)	105° C without applied voltage for 72 hours. EIA-364-17, method A	-

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	5
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved			PH

6.3.6	Mixed flowing gas	Samples should be placed in an environmentally controlled 'test chamber' that is monitored by a gas analyzing system for controlled concentrations of the specified gas mixture. Test coupons shall also be used and the weight gain reported. Test duration is 7 days. EIA 364-65, Class II A	Contact resistance: 50mΩ max.
6.3.7	Thermal disturbance	Cycle the connector or socket between 15 °C ±3 °C and 85 °C ± 3 °C, as measured on the part. Ramps should be a minimum of 2 °C per minute, and dwell times should ensure that the contacts reach the temperature extremes (a minimum of 5 minutes). Humidity is not controlled. Perform 10 such cycles.	Contact resistance: 50mΩ max.
6.3.8	Waterproof Test	Immerse the sample that be mounted in the specified enclosure in water as following conditions: Water depth: 1m, Time: 30 minutes In accordance with IEC60529:2013	No leakage, water seepage, no obvious water mark in the test fixture.
6.3.9	Dust-tight Test	Put sample in a closed chamber with suspended talcum powder as following conditions: Pump speed:40-60 times of the shell volume per hour Amount of talcum powder:2kg/m ³ Time:2 hours In accordance with IEC60529:2013	No ingress of dust
6.3.10	High Temperature Life	Temperature: +125 °C Duration: 1 hour Mated with plug, rating current is applied to the contacts as below: VBUS: 5A; GND: 6.25A Vconn pin:1.25A; Signal: 0.25A	No physical Damage Contact resistance: 50mΩ max.


PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	6
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved			PH

7.0 RESISTANCE TO INFRARED REFLOW SOLDERING HEAT

Parameter	Reference	Specification
Average temperature gradient in preheating		2.5°C/s
Soak time	T_{soak}	2-3 minutes
Time above 217°C	T_1	60 s
Time above 230°C	T_2	50 s
Time above 250°C	T_3	5 s
Peak temperature in reflow	T_{peak}	255°C(-0/+5°C)
Temperature gradient in cooling		-5°C/s max

Lead Free Process



This profile is the minimum requirement for evaluating soldering heat resistance of components. Heat transfer method used for reflow soldering is hot air convection. The actual air temperatures used to achieve the specified profile is higher and largely dependent on the reflow equipment.

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	7
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

8.0 PACKAGING AND PRECAUTIONS

8.1 The product is packed in tape and reel, put into moisture barrier bag and vacuum sealed together with desiccant & humidity indicator.

8.2 Precautions:

MSL rating: 3 (Non-JEDEC)

1. Recommended storage conditions before unpacking: +5°C to +30°C, maximum humidity 60%.
2. Recommended use within 168 hours after unpacking. For details, please refer to MSL label on packaging.
3. Connectors that have not been used up after 168 hours are suggested to be vacuum packed with desiccant. It is recommended that the parts are baked based on below process before reflow.
4. Baking process: remove tape and reel from vacuum sealed packaging and bake at 60°C ≤5% RH for 72 hours.
5. If floor life is not consistent with MSL rating 3 and above suggestions, air leakage performance post reflow will be impacted.

Packaging process



PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	8
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

Repackaging process

Unused connectors



Desiccant



Vacuum packed



Baking process

Unpack



Baking oven



9.0 PRODUCT QUALIFICATION AND TEST SEQUENCE

Note: each group test needs 5pcs samples.

Test No	Description	Requirement
Group A-1		
6.0.1	Examination	Visual inspection; No physical damage
6.1.1	LLCR	40mΩ Max all contacts
6.2.2	Durability (preconditioning)	50 cycles; No physical damage

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	9
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved			PH

6.3.5	Temperature Life	
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Reseating	No physical damage
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Examination	Visual inspection; No physical damage
Group A-2		
6.0.1	Examination	Visual inspection; No physical damage
6.1.1	LLCR	40mΩ Max all contacts
6.2.2	Durability (preconditioning)	50 cycles; No physical damage
6.3.3	Thermal Shock	
6.1.1	LLCR	50mΩ Max all contacts
6.3.1	Humidity	
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Reseating	No physical damage
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Examination	Visual inspection; No physical damage
Group A-3		
6.0.1	Examination	Visual inspection; No physical damage
6.1.1	LLCR	40mΩ Max all contacts
6.2.2	Durability (preconditioning)	50 cycles; No physical damage
6.3.5	Temperature Life (preconditioning)	
6.1.1	LLCR	50mΩ Max all contacts
6.2.3	Vibration	Discontinuity less than 1μs
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Examination	Visual inspection; No physical damage
Group A-4		
6.0.1	Examination	Visual inspection; No physical damage

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	10
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

6.1.1	LLCR	40mΩ Max all contacts
6.2.2	Durability (preconditioning)	50 cycles; No physical damage
6.3.5	Temperature Life (preconditioning)	
6.1.1	LLCR	50mΩ Max all contacts
6.3.6	Mixed Flowing Gases	
6.1.1	LLCR	50mΩ Max all contacts
6.3.7	Thermal Disturbance	
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Reseating	No physical damage
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Examination	Visual inspection; No physical damage
Group A-7		
6.0.1	Examination	Visual inspection; No physical damage
6.1.3	DWV	No breakdown or flashover
6.1.1	LLCR	40mΩ Max all contacts
6.2.2	Durability (preconditioning)	No physical damage
6.2.1	Insertion Force	Within the range of 5N to 20N.
6.2.1	Extraction force	Within the range of 8N to 20N. Initial Reading
6.2.2	Durability	25cycles, No physical damage
6.2.1	Extraction force	Within: a) 33% of initial reading & b) 8N to 20N
6.2.2	Durability	Perform 2468cycles and then rotate the plug or socket 180° and then perform 2500cycles. rotate the plug or socket 180° and then perform 2500cycles. rotate the plug or socket 180° and then perform 2500cycles. No physical damage (Replace the plug after 10K cycles)
6.2.1	Extraction force	Within the range of 6N to 20N.
6.1.1	LLCR	50mΩ Max all contacts
6.1.3	DWV	No breakdown or flashover
6.1.2	Insulation Resistance	100 MΩ Max.
6.0.1	Examination	Visual inspection; No physical damage

PRODUCT SPECIFICATION

Part Number	USB4731	Rev	A	Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin			Page	11
Doc Number	USB Type C	Prepared	CC	Checked	YR
		Approved	PH		

Group B-1		
6.0.1	Examination	Visual inspection; No physical damage
6.2.4	4-Axis Continuity	Discontinuity less than 1μs
6.0.1	Examination	Visual inspection; No physical damage
Group B-6		
6.0.1	Examination	Visual inspection; No physical damage
6.1.4	Contact Current Rating	The Temperature Rise shall not exceed 30°C
6.0.1	Examination	Visual inspection; No physical damage
Group C-1		
6.0.1	Examination	Visual inspection; No physical damage
6.3.8	Waterproof Test	No leakage, water seepage, no obvious water mark in the test fixture.
6.3.9	Dust-tight Test	No ingress of dust
Group C-2		
6.0.1	Examination	Visual inspection; No physical damage
6.1.1	LLCR	40mΩ Max all contacts
6.3.10	High Temperature Life	No physical damage
6.1.1	LLCR	50mΩ Max all contacts
6.2.2	Durability (preconditioning)	No physical damage
6.2.1	Insertion Force	Within the range of 5N to 20N.
6.2.1	Extraction force	Within the range of 8N to 20N. Initial Reading
6.2.2	Durability	25cycles, No physical damage
6.2.1	Extraction force	Within: a) 33% of initial reading & b) 8N to 20N
6.2.2	Durability	Perform 2468cycles and then rotate the plug or socket 180° and then perform 2500cycles. rotate the plug or socket 180° and then perform 2500cycles. rotate the plug or socket 180° and then perform 2500cycles. No physical damage (Replace the plug after 10K cycles)
6.2.1	Extraction force	Within the range of 6N to 20N.
6.1.1	LLCR	50mΩ Max all contacts
6.0.1	Examination	Visual inspection; No physical damage

PRODUCT SPECIFICATION

Part Number	USB4731			Rev	A		Date	18/05/26
Product Description	Type C Receptacle for USB2.0, With Shell Spring, SMT Type, Top Mount, Horizontal, IP67, 16 Pin					Page	12	
Doc Number	USB Type C	Prepared	CC	Checked	YR	Approved	PH	

Revision Details:

Revision	Information	Page	Release Date
0.1	First draft	-	25/09/2025
0.2	Updated after review	-	09/01/2026
A	First Release	-	18/05/2026