

USB Type-C™ to DisplayPort Adapter (DP Alt Mode) 8K 30 Hz with HDR function red

Description

This adapter by Delock is suitable for the connection of a DisplayPort monitor in 8K Ultra HD (7680 x 4320 @ 30 Hz) resolution to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Item no. 60052

EAN: 4043619600526

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x DisplayPort female
- DisplayPort 1.4 specification
- Contacts gold-plated
- Resolution up to:
 - 7680 x 4320 @ 30 Hz
 - 3840 x 2160 @ 144 Hz
 (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDR10
- Supports HDCP 1.4 and 2.2
- Plug & Play
- Housing material: aluminium
- Cable length without connectors: ca. 20 cm
- Colour: black / red

System requirements

- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode

or

- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to DisplayPort adapter

Images



General

Specification:	DisplayPort 1.4 HDCP 1.4 HDCP 2.2 HDR10 USB Type-C™
----------------	---

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x DisplayPort female

Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 30 Hz 3840 x 2160 @ 144 Hz
----------------------------	---

Physical characteristics

Housing material:	Aluminium
Pin finishing:	gold-plated
Length:	20 cm
Colour:	red black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de