

Flat suction cup (round)

PFYN 30 HT1-60 G1/8-AG

Part no.:10.01.01.11138

<https://www.schmalz.com/10.01.01.11138>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat suction cup (round) > Flat Suction

Cups PFYN > PFYN 30 HT1-60 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 30

Suction cup material:

High temp material HT1


Material hardness: 60 °Sh

Material property: imprint-free

Nipple material: Aluminium

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2.4 mm
Dmax(S)	31.5 mm
Ds	28.8 mm
G1	G1/8"-AG
H	17 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	2 mm

Technical Data

Flat suction cup (round)

PFYN 30 HT1-60 G1/8-AG

Part no.:10.01.01.11138


<https://www.schmalz.com/10.01.01.11138>



Attribute	Value
Suction force (-600mbar)	34 N
Volume	1.3 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (empf.) d	4 mm
Size	30
Number of folds	0
Suction cup material	High temp material HT1
Material hardness [Shore A]	60 Shore A
Weight	7.9 g
Product family	PFYN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SA-NIP N007 G1/8-AG DN240

Part no.10.01.01.03531

Suction cup connection nipple

Nipple: N 007

Thread G1: G1/8"-M

Overall length: 21.5 mm

Fitting length: 5 mm

Nominal size: 2,40 mm

Material: Aluminium

Spanner size SW2: 4 mm

Flat suction cup (round)

PFYN 30 HT1-60 G1/8-AG

Part no.:10.01.01.11138

<https://www.schmalz.com/10.01.01.11138>



PFG 30 HT1-60 N007

Part no.10.01.01.11165

Flat suction cup (round) for smooth or slightly rough surfaces

Size: 30

Suction cup material:

High temp material HT1

Material hardness: 60 °Sh

Material property: imprint-free

Accessories



SU 30

Part no.10.01.01.12889

Cover for suction cup

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C