

VKA00C25
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON ONE SIDE

, 10m, M12 Female (socket) 12pin Straight, Free conductor end, 12x0.14mm², PUR (Polyurethane), Ø5.8mm, 30V, 90°C, IP67, Suitable for trailing chain and torsion resistant, Oil and cooling lubricants, Welding area, Silicone-free


MECHANICAL FEATURES

Cable infeed of A connection	Straight
Cable length	10 m
Degree of protection (IP)	IP67
Material of cable sheath	PUR (Polyurethane)
Number of cores	12
Perm. ambient temperature of cable, fixed cable	-25 °C ... 90 °C
Suitable for trailing chain	+
Torsion cycles	+/-180°/m, ≥ 0.5 million cycles
Trailing chain cycles	≥ 2 million cycles
Version	Connection cable
Wire assembly	72 x 0.05mm
Wire cross section	0.14 mm ²

ELECTRICAL FEATURES

Line diameter	5.8 mm
Number of pins of A connection	12
Rated current	1.5 A
Rated voltage	30 V
Type of A electrical connection	M12
Type of B electrical connection	Free conductor end
Type of plug-in contact, A connection	Female (socket)

OTHER FEATURES

Flame retardant	In accordance with EN 60332-2-2
Free of LABS	+
Halogen-free	+
Hydrolysis-proof	+
IR-networked	-
Oil and cooling lubricants	+
Ozone and UV-resistant	+
Silicone-free	+
Suitable for trailing chain and torsion resistant	+
Welding area	+


Other

Packaging dimensions	0.0mm x 0.0mm x 0.0mm
Shipping weight	0.38kg
Tariff code	85444290


Classification

ipf product group	856
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection



Dimensional drawing



Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.