

5
kWh/1000h

A+
energy class

76
lumens/watt

GU10 Start

LED Start GU10 5W(50) 865 35° TU 1/8
93094491

Product information

This new entry level range of highly competitive LED GU10 and R50 products consume only 3.5W and 5W respectively and offer a fantastic energy saving alternative to 50W and 35W Halogen GU10 lamps.

Application areas



Retail



Office



Hospitality



Home

Product data

Product Code	93094491
Bulb Shape	PAR
Bulb Finish	White
Bulb maximum overall diameter [mm]	50
Nominal Length [mm]	53
Net weight per piece [g]	29
RoHS compliant	Yes
Brand	Tungsram
Cap/Base	GU10

Performance data

Nominal/ Rated Beam Angle [°]	35
Nominal center beam candlepower (CBCP) [cd]	700
Rated Lumens [lm]	360
Weighted energy consumption [kWh/1000h]	5.0
Useful lumens (at 90° cone) [lm]	360
Rated efficacy [lm/W]	72
Energy efficiency class (EEC)	A+
Rated life L70/B50 [h]	15 000
Nominal correlated colour temperature (CCT) [K]	6500
Nominal lumens [lm]	380
Colour Rendering Index (CRI) [Ra]	80


Electrical data

Nominal lamp power factor...	0.5
Rated power [W]	5.0
Number of switching cycles	50 000
Dimming Capability	No
Nominal lamp voltage range [V]	220-240
Nominal power [W]	5.0

Logistic data

DUN Code	20064894509616
EAN Code	0064894509612
Pack Quantity	8
Inner pack type	Box
Product status	Available

Photometric Data



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Photometry \(IES\)](#)

[Product datasheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Images \(HTTP\)](#)

[Doc documents \(PDF\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)