




Product: [H121C00](#)



H121C00 - Broadband Coax, H121, 20 AWG Solid BC, CU-Foil + 45% BC Braid, PVC Jkt

Product Description

Broadband Coax, H121, 20 AWG Solid Bare Copper Conductor, PE Insulation, Copper Foil + 45% Bare Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Over-The-Air (OTA) antennas
------------------------	--

Construction Details

RG Type:	59
Series Type:	59

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	21 AWG	Solid	0.8 mm	BC - Bare Copper

Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	3.5 mm (0.14 in)

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Tape	Bi-Laminate (Bare Copper+Poly)	100%
2	Braid	Bare Copper (BC)	45%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	5 mm

Table Notes:	According to European Standard EN 50290-2-20
--------------	--

Electrical Characteristics

Regularity of Impedance:	Min. 40 dB
--------------------------	------------

Return Loss (RL)

Frequency	Min. Return Loss
5 - 470 MHz	20 dB
470 - 1000 MHz	18 dB
1000 - 2000 MHz	16 dB
2000-3000 MHz	15 dB

Table Notes:	In each frequency band, 3 peak values up to 4 dB lower are allowed
--------------	--

Attenuation

Frequency	Nom. Attenuation
5 MHz	1.7 dB/100m
50 MHz	5.3 dB/100m
100 MHz	7.6 dB/100m

200 MHz	10.8 dB/100m
400 MHz	15.4 dB/100m
600 MHz	19.1 dB/100m
800 MHz	22.2 dB/100m
1000 MHz	25 dB/100m
1350 MHz	29.3 dB/100m
1600 MHz	32.2 dB/100m
1750 MHz	33.8 dB/100m
2150 MHz	37.8 dB/100m
2400 MHz	40.1 dB/100m

Table Notes:	Max. attenuation 10% higher
--------------	-----------------------------

Electricals

Max. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
35 Ohm/km (11 Ohm/1000ft)	24 Ohm/km (7.3 Ohm/1000ft)	53 pF/m (16 pF/ft)	75 Ohm	84%

Transfer Impedance

Frequency	Max. Transfer Impedance
5-30 MHz	Max. 10 mOhm/m

Screening

Frequency	Min. Screening Attenuation
30 - 1000 MHz	85 dB

Screening Class:	B
------------------	---

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +70°C	-5°C To +50°C	-40°C To +70°C

Bend Radius

Stationary Min.
50 mm (2.0 in)

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
CENELEC Compliance:	EN 50117-1, EN 50117-9-2, EN 50290-2-20
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.207 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
H121C00.00B100	White	Flat Box	100 m	8719605085764