

Control cable | PUR | chainflex® CF77.UL.D

36 10 million
Double strokes guaranteed

6.8 x d
Bend radius, e-chain®

100m
Travel distance, e-chain®

- For heavy duty applications
- PUR outer jacket
- Oil-resistant and coolant-resistant
- Flame-retardant
- PVC and halogen-free
- Notch-resistant
- Hydrolysis and microbe-resistant

Dynamic information

	Bend radius	e-chain® linear	minimum 6.8 x d
		flexible	minimum 5 x d
		fixed	minimum 4 x d
	Temperature	e-chain® linear	-25°C up to +80°C
		flexible	-40°C up to +80°C (following DIN EN 60811-504)
		fixed	-50°C up to +80°C (following DIN EN 50305)
	v max.	unsupported	10m/s
	a max.	gliding	5m/s
			80m/s²
	Travel distance	Unsupported travels and up to 100m for gliding applications, Class 5	
	Torsion	Torsion ±180°, with 1m cable length, Class 3 (except for 5-core types ≥ 4.0mm² ► Product range table)	

Cable structure

	Conductor	Finely stranded conductor consisting of bare copper wires (following DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	Number of cores < 12: Cores wound in a layer with short pitch length. Number of cores ≥ 12: Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions. Especially low-torsion structure.
	Core identification	Cores < 0.5mm²: Colour code in accordance with DIN 47100. Cores ≥ 0.5mm²: Black cores with white numbers, one green-yellow core. CF77.UL.02.03.INI: brown, blue, black CF77.UL.03.04.INI: brown, blue, black, white CF77.UL.03.05.INI: brown, blue, black, white, green-yellow
	Outer jacket	Low-adhesion, halogen-free, highly abrasion resistant PUR mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-10-2) Colour: Window-grey (similar to RAL 7040) Variants ► Product range table

Electrical information

	Nominal voltage	300/500V (following DIN VDE 0298-3) Number of cores < 12: Cores < 0.5mm²: 300V (following UL) Cores ≥ 0.5mm²: 1000V (following UL) Number of cores ≥ 12: 1000V (following UL)
	Testing voltage	2,000V (following DIN EN 50395)

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	7	≥ 400m
none	1	2	3	4	highest			
none	1	2	3	4	±360°			

Class 5.5.2.1

Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-10-2), Class 3
	Offshore	MUD-resistant following NEK 606 - status 2016
	Flame-retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	Halogen-free	Following DIN EN 60754
	UL verified	Certificate No. B129699: "igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year"
	UL/CSA AWM	See data sheet for details ► www.igus.eu/CF77ULD
	NFPA	Following NFPA 79-2018, chapter 12.9
	DNV	Type Approval Certificate TAE00003X1
	EAC	Certificate No. RU C-DE.ME77.B.00300/19
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1, material/cable tested by IPA according to DIN EN ISO standard 14644-1
	DESINA	According to VDW, DESINA standardisation
	CE	Following 2014/35/EU
	UKCA	In accordance with the valid regulations of the United Kingdom (as at 08/2021)

Guaranteed service life (details see page 28-29)

Double strokes*	5 million		7.5 million		10 million	
	< 10m	≥ 10m	< 10m	≥ 10m	< 10m	≥ 10m
Temperature, from/to [°C]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]
-25/-15	8.5	10	9.5	11	10.5	12
-15/+70	6.8	7.5	7.5	8.5	8.5	9.5
+70/+80	8.5	10	9.5	11	10.5	12

* Higher number of double strokes? Service life calculation online ► www.igus.eu/chainflexlife

Typical application areas

- For heavy-duty applications, Class 5
- Unsupported travels and up to 100m for gliding applications, Class 5
- Almost unlimited resistance to oil, Class 3
- Torsion ±180°, with 1m cable length, Class 3
- Indoor and outdoor applications with average sun radiation
- Machining units/machine tools, storage and retrieval units for high-bay warehouses, packaging industry, quick handling, refrigerating sector

Guarantee
igus chainflex
36
months

igus 36-month
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year

CFRIP

UL LISTED

UL

nec

NFPA

CUPA

DNV

EAC

REACH

RoHS

clean-room

DESINA

CE

UKCA

Control cable | PUR | chainflex® CF77.UL.D

Class 5.5.2.1

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	≥ 400m	
none	1	2	3	4	highest			
none	1	2	3	4	±360°			



Example image

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF77.UL.02.03.INI ¹²⁾	3x0.25	5.0	9	29
CF77.UL.02.04.D	4x0.25	5.5	11	35
CF77.UL.02.05.D	5x0.25	6.0	13	39
CF77.UL.02.07.D	7x0.25	6.5	18	51
CF77.UL.02.12.D	12x0.25	9.0	32	78
CF77.UL.02.18.D	18x0.25	10.5	47	127
CF77.UL.02.25.D	25x0.25	11.5	63	155
CF77.UL.03.04.INI ¹²⁾	4x0.34	6.0	14	37
CF77.UL.03.05.INI ¹²⁾	5x0.34	6.0	18	36
CF77.UL.03.05.INI.D	5x0.34	6.0	18	36
CF77.UL.05.04.D	4G0.5	6.0	21	46
CF77.UL.05.05.D	5G0.5	6.5	26	53
CF77.UL.05.07.D	7G0.5	7.5	39	78
CF77.UL.05.12.D	12G0.5	10.0	63	130
CF77.UL.05.18.D	18G0.5	12.0	94	184
CF77.UL.05.25.D	25G0.5	14.0	129	243
CF77.UL.05.30.D	30G0.5	15.0	155	315
CF77.UL.07.03.D	3G0.75	6.5	23	52
CF77.UL.07.04.D	4G0.75	7.0	31	59
CF77.UL.07.05.D	5G0.75	7.5	38	71
CF77.UL.07.07.D	7G0.75	8.5	54	100
CF77.UL.07.12.D	12G0.75	12.0	91	180
CF77.UL.07.18.D	18G0.75	13.5	134	239
CF77.UL.07.20.D	20G0.75	14.5	149	269
CF77.UL.07.25.D	25G0.75	16.0	186	336
CF77.UL.07.36.D	36G0.75	19.0	279	506
CF77.UL.07.42.D	42G0.75	21.0	341	580
CF77.UL.10.02.D	2x1.0	6.5	21	51
CF77.UL.10.03.D	3G1.0	6.5	31	58
CF77.UL.10.04.D	4G1.0	7.0	41	73
CF77.UL.10.05.D	5G1.0	8.0	50	90
CF77.UL.10.07.D	7G1.0	9.0	71	120
CF77.UL.10.12.D	12G1.0	12.5	120	220
CF77.UL.10.18.D	18G1.0	15.0	179	314
CF77.UL.10.25.D	25G1.0	17.5	248	431
CF77.UL.10.42.D	42G1.0	22.5	433	699

¹²⁾ Colour outer jacket: Colza yellow (similar to RAL 1021)

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF77.UL.15.03.D	3G1.5	7.0	46	71
CF77.UL.15.04.D	4G1.5	7.5	61	88
CF77.UL.15.05.D	5G1.5	8.0	75	105
CF77.UL.15.07.D ¹⁷⁾	7G1.5	9.5	105	152
CF77.UL.15.12.D	12G1.5	13.0	179	297
CF77.UL.15.18.D	18G1.5	17.0	268	405
CF77.UL.15.25.D	25G1.5	19.5	297	564
CF77.UL.15.36.D	36G1.5	23.5	551	848
CF77.UL.25.03.D	3G2.5	8.5	75	132
CF77.UL.25.04.D	4G2.5	9.5	95	167
CF77.UL.25.05.D	5G2.5	10.0	124	196
CF77.UL.25.07.D ¹⁷⁾	7G2.5	12.0	174	270
CF77.UL.25.12.D	12G2.5	17.0	297	479
CF77.UL.40.04.D ⁹⁰⁾	4G4.0	11.5	165	245
CF77.UL.40.05.D ⁹⁰⁾	5G4.0	12.0	198	284
CF77.UL.60.05.D ⁹⁰⁾	5G6.0	13.5	297	412

¹⁷⁾ When using the cables with "7G1.5mm²" and "7G2.5mm²" minimum bend radius must be 17.5xd with gliding travel distance ≥ 5m.
⁹⁰⁾ Torsion ± 90°

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core



Cables available in the chainflex® CASE

Simple savings on delivery, storage space and re-ordering with the chainflex® CASE - ship'n store by igus®.

More on this on page 24/25 and online: www.igus.eu/cf-case



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year