

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect standard, CCS type 2, DC charging cable, 150 A permanent, 1000 V DC, with vehicle charging connector and open cable end, cable: 7 m, black, straight, with four-wire measurement technology, with analog temperature sensors, with replaceable mating face frame, with replaceable DC power contacts, with connected PP contact, PHOENIX CONTACT logo, IEC 62196-3, for charging electric vehicles (EV) with direct current (DC), IP67 degree of protection

Product description

DC charging cable with vehicle charging connector and free cable end for fast charging of electric vehicles (EV) with direct current (DC) via CCS type 2 vehicle charging inlets, for installation at charging stations for e-mobility (EVSE)

Your advantages

- Broad portfolio for all DC charging applications in the medium power range
- Particularly robust and durable connector design for high availability
- Prepared for four-wire measurement technology, enabling simple billing compliant with calibration laws
- High-level safety with two-chamber sealing system for the separation of DC+ and DC-
- Fast and cost-effective maintenance with exchangeable mating face including power contacts
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001

Commercial data

Item number	1674676
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	XWBMHD
Product key	XWBMHD
GTIN	4067923224766
Weight per piece (including packing)	10,894 g
Weight per piece (excluding packing)	9,898 g
Customs tariff number	85444290
Country of origin	Information on the country of origin is provided with the delivery.

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Technical data

Notes

General	IP67 degree of protection
---------	---------------------------

Product properties

Product type	DC charging cable
Product family	CHARX connect standard
Type	DC charging cable with vehicle charging connector and open cable end
Design	with four-wire measurement technology with analog temperature sensors with replaceable mating face frame with replaceable DC power contacts with connected PP contact no liquid cooling
Charging standard	CCS type 2
Charging mode	Mode 4
Affixed logo	PHOENIX CONTACT logo

Electrical properties

Temperature monitoring	2x Pt 1000
------------------------	------------

Charging power and current (DC charging)

Type of charging current	DC
Charging current	150 A DC
Charging power	150 kW
Rated voltage	1000 V

Charging power and current (DC charging in Boost Mode)

Type of charging current	DC Boost Mode
--------------------------	---------------

Pin assignment (Power contacts)

Note on the connection method	Crimp connection, cannot be disconnected
Number	3 (PE, DC+, DC-)
Rated voltage	1000 V DC
Rated current	150 A (up to 40 °C)

Pin assignment (Signal contacts)

Note on the connection method	Crimp connection, cannot be disconnected
Type of signal transmission	Pulse width modulation with modulated Powerline communication in accordance with ISO/IEC 15118 / DIN SPEC 70121
Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Coding	1500 Ω (between PE and PP)
	PP signal contact connected to cable

Temperature sensors (Pt 1000)

Sensor type	Pt 1000
Standards/regulations	DIN EN 60751
Attachment point	2 sensors for the DC contacts
Switch-off temperature	90 °C

Dimensions

Vehicle charging connector

Width	72 mm
Height	181.1 mm
Depth	285.3 mm

Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Mating face)	black (9005)
Color (Cable)	black (9005)
Material (Vehicle charging connector)	Plastic
Material (Cable outer sheath)	TPE-U
Material (Contact surface)	Silver
Note	The color appearance and gloss level of the charging cable may vary.
Flammability rating according to UL 94	V0 (Mating face)

Cable/line

Cable length	7 m $\pm$ 50 mm
Wiring standards/regulations	DIN EN 50620
Wiring certifications	VDE-Reg.
Cable type	Class 6
Cable type	straight
Cable structure	2 x 35 mm ² + 1 x 16 mm ² + 2 x 0.75 mm ² + 6 x 0.5 mm ²
External cable diameter	26.10 mm $\pm$ 0.5 mm
Outer sheath, material	TPE-U
Stripping length of the sheath	180 mm $\pm$ 10 mm
Stripping length	180 mm $\pm$ 10 mm
Cable resistance	0.000272 Ω /m
Bending radius	261 mm $\pm$ 1 mm (10 x D)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
-----------------------------	---------

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions

Degree of protection (Vehicle charging connector)	IP67 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Ambient temperature (operation)	-30 °C ... 40 °C max. 55 °C (Current reduction required, observe the DC contact temperature limit value of 90°C)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	max. 5000 m (above sea level)

Standards and regulations

Standards/specifications	IEC 62196-3
Note	Compliant with AFIR - EU 2025/656


CHARX ST2C-DC150-7,0MCS00P - DC charging cable

1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Drawings

Schematic diagram



Operating instructions

CHARX ST2C-DC150-7,0MCS00P - DC charging cable

1674676


<https://www.phoenixcontact.com/gb/products/1674676>

Schematic diagram



The Combined Charging System (CCS) principle - standard-compliant charging system for electric vehicles, which supports both conventional AC charging and fast DC charging. Both Vehicle Connectors fit into the CCS Vehicle Inlet.

Schematic diagram




Pin assignment of the Vehicle Connector

CHARX ST2C-DC150-7,0MCS00P - DC charging cable

1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Schematic diagram



Warnings regarding use

CHARX ST2C-DC150-7,0MCS00P - DC charging cable

1674676

<https://www.phoenixcontact.com/gb/products/1674676>

Schematic diagram



The resting position must be installed in the charging station such that the user cannot hang up the vehicle connector upside down (90° to 270°). However, positions rotated upward (45°) or downward (315°) are options for a resting position.

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676
<https://www.phoenixcontact.com/gb/products/1674676>

Classifications

ECLASS

ECLASS-13.0	27144705
ECLASS-15.0	27144705

ETIM

ETIM 10.0	EC002897
-----------	----------

CHARX ST2C-DC150-7,0MCS00P - DC charging cable



1674676
<https://www.phoenixcontact.com/gb/products/1674676>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk