



BRIGHTTEK
BRIGHTTEK (EUROPE) LIMITED

Brighten up The World With LED!



ISO/TS 16949:2009



BS EN ISO 14001:2004



QC 080000 IECQ HSPM

PRODUCT DATASHEET




- ▶ PCB / CHIP LED
- ▶ 0603+Lens (1608) 0.95t
- ▶ Red 622nm

NOR69S03



Release Date: 17 June 2026 Version: A1.1



APPLICATIONS:

- Indication Light
- Switch light
- Dashboard

0603+Lens (1608) 0.95t



FEATURES:

- **Package:** PCB / CHIP LED Top View
- **Forward Current:** 20mA
- **Forward Voltage (typ.):** 2.0V
- **Luminous Intensity (typ.):** 715mcd@20mA
- **Colour:** Red
- **Dominant Wavelength (typ.):** 622nm
- **Viewing Angle:** 55°
- **Materials:**
 - Resin: Epoxy (Water Clear)
- **Operating Temperature:** -40~+85°C
- **Storage Temperature:** -40~+100°C
- **Grouping Parameters:**
 - Forward voltage
 - Luminous intensity
 - Dominant wavelength
- **Soldering Methods:** Reflow
- **MSL:** Level 2a acc. to JEDEC
- **Packing:** 8mm tape with max.4000/reel, ø178mm (7")

CHARACTERISTICS:

Absolute Maximum Characteristics ($T_a=25^{\circ}\text{C}$)

Parameter	Symbol	Ratings	Unit
Forward Current	I_F	20	mA
Peak Forward Current (duty 1/10; 1kHz)	I_{FP}	100	mA
Reverse Voltage	V_R	5	V
Reverse Current	I_R	10	μA
Power Dissipation	P_D	48	mW
Operating Temperature	T_{OPR}	$-40^{\circ}\sim+85^{\circ}$	$^{\circ}\text{C}$
Storage Temperature	T_{STG}	$-40^{\circ}\sim+100^{\circ}$	$^{\circ}\text{C}$

Electrical & Optical Characteristics ($T_a=25^{\circ}\text{C}$)


Parameter	Symbol	Values			Unit	Test Condition
		Min.	Typ.	Max.		
Forward Voltage	V_F	---	2.0	2.4	V	$I_F=20\text{mA}$
Luminous Intensity	I_V	---	715	---	mcd	$I_F=20\text{mA}$
Dominant Wavelength	λ_D	---	622	---	nm	$I_F=20\text{mA}$
Peak Wavelength	λ_P	---	630	---	nm	$I_F=20\text{mA}$
Spectrum Radiation Bandwidth	$\Delta\lambda$	---	20	---	nm	$I_F=20\text{mA}$
Viewing Angle (X/Y)	$2\theta_{1/2}$	---	55	---	deg	$I_F=20\text{mA}$

1. Luminous intensity (I_V) $\pm 10\%$, Forward Voltage (V_F) $\pm 0.1\text{V}$.




OUTLINE DIMENSION:

Package Dimension:



Recommended Soldering Pad Dimension:



BINNING GROUPS:

Forward Voltage Classifications ($I_F = 20\text{mA}$):

Code	Min.	Max.	Unit
E18	1.6	2.4	V

Luminous Intensity Classifications ($I_F = 20\text{mA}$):


Code	Min.	Max.	Unit
V	450	560	mcd
W	560	715	
X	715	900	
Y	900	1125	
Z	1125	1440	

Dominant Wavelength Classifications ($I_F = 20\text{mA}$):


Code	Min.	Max.	Unit
AD	615	635	nm

ELECTRO-OPTICAL CHARACTERISTICS:


Relative Intensity v.s. Forward Current




Forward Current v.s. Forward Voltage




Temperature Derating Chart




Relative Intensity v.s. Wavelength



Relative Intensity v.s. Angular Displacement (X)




Relative Intensity v.s. Angular Displacement (Y)





RECOMMENDED SOLDERING PROFILE:

Reflow solder:




Note:

1. Recommend reflow temperature 240°C. The maximum soldering temperature should be limited to 260°C.
2. Maximum reflow soldering: 2 times.
3. Before, during, and after soldering, should not apply stress on the components and PCB board.



PACKING SPECIFICATION:

Reel Dimension:



PRECAUTIONS OF USE:

Storage:

It is recommended to store the products in the following conditions:

- Humidity: 60% R.H. Max.
- Temperature: 5°C~30°C (41°F ~86°F).

Shelf life in sealed bag: 12 months at 5°C~30°C and <60% R.H.

Once the package is opened, the products should be used within 4 weeks. Otherwise, they should be kept in a damp-proof box with desiccating agent <10% R.H. and apply baking before use.

Baking:

It is recommended to bake the LED before soldering if the pack has been unsealed for longer than 24hrs. The suggested baking conditions are as follows:

- 60±5°C x 12~24hrs and <5%RH, taped / reel package.

It's normal to see slight color fading of carrier (light yellow) after baking in process.

Testing Circuit:



Must apply resistor(s) for protection (over current proof).

Cleaning:

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED carrier / package. Avoid putting any stress force directly on to the LED lens.

ESD (Electrostatic Discharge):

Static Electricity or power surge will damage the LED. Use of a conductive wrist band or anti-electrostatic glove is recommended when handling the LED all time. All devices, equipment, machinery, work tables, and storage racks must be properly grounded.

In the events of manual working in process, make sure the devices are well protected from ESD at any time.

REVISION RECORD:

Version	Date	Summary of Revision
A1.0	08/08/2022	Datasheet set-up.
A1.1	17/06/2026	New datasheet format.