

ISM 433 MHz Antenna SMA 3 dBi omnidirectional fixed magnetic base black

Description

This antenna by Delock allows the usage of 433 MHz band indoors and outdoors.



Item no. 88877

EAN: 4043619888771

Country of origin: China

Package: Retail Box

Technical details

- Connector: SMA plug
- Frequency range: 433 MHz
- Gain: 3 dBi
- Impedance: 50 Ohm
- VSWR: 2.0
- Polarisation: linear, vertical
- Operation temperature: -10 °C ~ 75 °C
- Cable colour: black
- Cable type: RG-174
- Cable length: ca. 3 m
- Antenna length: ca. 12.4 cm
- Antenna length including magnetic base: ca. 15 cm
- Diameter (base): ca. 3 cm

System requirements

- Device with one free SMA jack

Package content

- Antenna

Images



General

Mounting type:	magnetic
Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	433 MHz
Antenna gain:	3 dBi
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 75 °C
Polarisation:	vertical linear
VSWR:	2.0

Physical characteristics

Antenna type:	omnidirectional
Antenna length including magnetic base:	15 cm
Diameter magnetic base:	3.0 cm
Cable category:	coaxial
Cable type:	RG-174
Cable colour:	black
Cable length incl. connectors:	3 m
Length:	12.4 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

