

S/PDIF TOSLINK Splitter 1 In 3 Out with USB Powered

Description

With this TOSLINK splitter by Delock up to three TOSLINK devices can be operated at the same time at one TOSLINK output.

Supports HD audio formats

The splitter supports all popular **2.0** and **5.1** audio formats such as **LPCM**, **Dolby Digital**, **DTS Audio** and therefore offers a sound experience like in a cinema.

High resolution sampling rate

The splitter offers a sampling rate of up to **24 bit** and **96 kHz**. This allows a loss-free playback of the sound in the High-Res audio range.

High transmission distance

The splitter supports an output transmission distance of up to **40 m** via an optical TOSLINK cable with a signal loss of less than 0.2 dB / m.

USB powered

The splitter does not require an additional external power supply, power will be supplied via the included USB cable.



Item no. 63397

EAN: 4043619633975

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - Input:
 - 1 x TOSLINK female S/PDIF
 - 1 x USB Type Mini-B female (5 V power supply)
 - Output: 3 x TOSLINK female S/PDIF
- Supported sample rates: 32 / 44.1 / 48 / 96 kHz
- Bit rate 16 - 24 Bit
- Baud rate: max. 16 Mbps
- Supports all common 2.0 and 5.1 audio formats: LPCM, Dolby Digital, DTS Audio
- Supports signal retiming
- On / Off switch
- Power LED (blue)
- Plastic housing
- Colour: black
- Dimensions (LxWxH): ca. 61 x 54 x 20 mm

- Voltage: 5 V
- Surge Protection
- USB bus powered


System requirements

- Digital optical audio signal
- A free USB Type-A female port

Package content

- TOSLINK splitter
- USB Type-A to Type Mini-B cable, length ca. 75 cm
- User manual

Images



General

Specification:	DTS Audio Dolby Digital LPCM
LED indicator:	Power

Interface

Output:	3 x TOSLINK female S/PDIF
Input:	1 x TOSLINK female S/PDIF 1 x USB Type Micro-B female (5 V power supply)

Technical characteristics

Bit rate:	16 - 24 Bit
Data transfer rate:	max. 16 Mbps
Voltage supply:	USB bus powered
Sample rate:	32 / 44,1 / 48 / 96 kHz

Physical characteristics

Housing colour:	black
Length:	61 mm
Width:	54 mm
Height:	20 mm
LED colour:	blue

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

