

Adapter USB 2.0 Type-A to 1 x serial RS-232 DB9 4 m

Description

This USB Type-A to serial adapter by Delock provides an RS-232 port for meters, POS systems, printers, modems, IoT devices etc.



4 m

Item no. 66323

EAN: 4043619663231

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x serial RS-232 DB9 male with screws
- Chipset: FTDI FT232
- Data transfer rate up to 460,8 Kbps
- Signals: TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
- Parity: even, odd, none, mark, space
- Stop bits: 1, 2
- Databits: 7, 8
- Flow control: none, Xon / Xoff, RTS / CTS
- FIFO: 128 Byte - RX
- FIFO: 256 Byte - TX
- Cable length incl. connectors: ca. 4 m


System requirements

- Linux Kernel 2.6 or above
- Mac OS 10.9 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB 2.0 to 1 x serial adapter
- Driver CD
- User manual

Images



General

Function:	Plug & Play
Specification:	USB 1.1 USB 2.0
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x Serial RS-232 DB9 male

Technical characteristics

Chipset:	FTDI 232R
Data transfer rate:	460.8 Kbps
FIFO:	128 byte 256 Byte
Data transmission:	asynchronous Bidirectional
UART:	USB to serial UART

Physical characteristics

Cable type:	UL AWM 2725 80 °C 30V VW-1
Cable colour:	black
Cable length:	4 m
Pin finishing:	gold-plated

Shielding:	double
Colour:	grey black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de