


Fibre optic diffuse reflection sensor

FT-30-A-A-M8



Application

Function principle	Diffuse reflection sensor
Application	High temperature resistance; Robust design for use in harsh industrial environments

Detection zone

Range with fibre optic amplifier type	OIF
---------------------------------------	-----

OIF

Range fibre optics [mm]	70
-------------------------	----

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Weight [g]	94.5
Version of sensing head	straight
Sensing head thread	M8
Total length [mm]	600
Min. bending radius [mm]	30; (for fixed installation)
Fibre arrangement	⓪
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium

E20152



Fibre optic diffuse reflection sensor

FT-30-A-A-M8

Fibre sheath material	aluminium
Accessories	
Items supplied	hexagon nuts: 2 x M8, stainless steel
	tooth lock washers: 2
	knurled nut: 1 x M30
Remarks	
Pack quantity	1 pcs.