



BRIGHTTEK

BRIGHTTEK (EUROPE) LIMITED

Brighten up The World With LED!



ISO/TS 16949:2009



BS EN ISO 14001:2004



QC 080000 IECQ HSPM

PRODUCT DATASHEET



- ▶ PCB / CHIP LED
- ▶ 0201 (0603) 0.36t
- ▶ Blue 470nm

NOB68S81-2MA



Release Date: 25 June 2026 Version: A1.0



APPLICATIONS:

- Backlighting
- Indication Light
- Switch light
- Dashboard

0201 (0603) 0.36t

RoHS
Compliant



FEATURES:

- **Package:** PCB / CHIP LED Top View
- **Forward Current:** 2mA
- **Forward Voltage (typ.):** 2.6V
- **Luminous Intensity (typ.):** 11.25mcd@2mA
- **Colour:** Blue
- **Dominant Wavelength (typ.):** 468nm
- **Viewing Angle:** 110°
- **Materials:**
 - Resin: Epoxy (Water Clear)
- **Operating Temperature:** -40~+85°C
- **Storage Temperature:** -40~+100°C
- **Grouping Parameters:**
 - Forward voltage
 - Luminous intensity
 - Dominant wavelength
- **Soldering Methods:** Reflow Soldering
- **MSL:** Level 2a acc. to JEDEC
- **Packing:** 8mm tape with max.4000/reel, ø178mm (7")

CHARACTERISTICS:

Absolute Maximum Characteristics ($T_a=25^{\circ}\text{C}$)

Parameter	Symbol	Ratings	Unit
Forward Current	I_F	2	mA
Peak Forward Current (duty 1/10; 1kHz)	I_{FP}	15	mA
Reverse Voltage	V_R	5	V
Reverse Current	I_R	10	μA
Power Dissipation	P_D	6.4	mW
Operating Temperature	T_{OPR}	-40~+85	$^{\circ}\text{C}$
Storage Temperature	T_{STG}	-40~+100	$^{\circ}\text{C}$


Electrical & Optical Characteristics ($T_a=25^{\circ}\text{C}$)

Parameter	Symbol	Values			Unit	Test Condition
		Min.	Typ.	Max.		
Forward Voltage	V_F	---	2.6	3.2	V	$I_F=2\text{mA}$
Luminous Intensity	I_v	---	11.25	---	mcd	$I_F=2\text{mA}$
Dominant Wavelength	λ_D	---	468	---	nm	$I_F=2\text{mA}$
Peak Wavelength	λ_P	---	463	---	nm	$I_F=2\text{mA}$
Spectrum Radiation Bandwidth	$\Delta\lambda$	---	16	---	nm	$I_F=2\text{mA}$
Viewing Angle	$2\theta_{1/2}$	---	110	---	deg	$I_F=2\text{mA}$

1. Luminous intensity (I_v) $\pm 10\%$, Forward Voltage (V_F) $\pm 0.1\text{V}$.


OUTLINE DIMENSION:

Package Dimension:



1. All dimensions are in millimetre (mm).
2. Tolerance $\pm 0.2\text{mm}$, unless otherwise noted.

Recommended Soldering Pad Dimension:



1. Dimensions are in millimetre (mm).
2. Tolerance $\pm 0.1\text{mm}$ with angle tolerance $\pm 0.5^\circ$.

BINNING GROUPS:

Forward Voltage Classifications ($I_F = 2\text{mA}$):

Code	Min.	Max.	Unit
G5	2.4	2.6	V
G6	2.6	2.8	
H5	2.8	3.0	
H6	3.0	3.2	

Luminous Intensity Classifications ($I_F = 2\text{mA}$):


Code	Min.	Max.	Unit
K	7.15	11.25	mcd
L	11.25	18.0	
M	18.0	28.5	

Dominant Wavelength Classifications ($I_F = 2\text{mA}$):


Code	Min.	Max.	Unit
AA	460	465	nm
AB	465	470	
AC	470	475	

ELECTRO-OPTICAL CHARACTERISTICS:


Relative Intensity vs. Forward Current




Forward Current vs. Forward Voltage




Temperature Derating Chart




Relative Intensity vs. Wavelength



Relative Intensity vs. Angular Displacement (X)




Relative Intensity vs. Angular Displacement (Y)





RECOMMENDED SOLDERING PROFILE:

Reflow solder:




Note:

1. Recommend reflow temperature 240°C. The maximum soldering temperature should be limited to 260°C.
2. Maximum reflow soldering: 2 times.
3. Before, during, and after soldering, should not apply stress on the components and PCB board.

PACKING SPECIFICATION:

Reel Dimension:



PRECAUTIONS OF USE:

Storage:

It is recommended to store the products in the following conditions:

- Humidity: 60% R.H. Max.
- Temperature: 5°C~30°C (41°F ~86°F).

Shelf life in sealed bag: 12 months at 5°C~30°C and <60% R.H.

Once the package is opened, the products should be used within 4 weeks. Otherwise, they should be kept in a damp-proof box with desiccating agent <10% R.H. and apply baking before use.

Baking:

It is recommended to bake the LED before soldering if the pack has been unsealed for longer than 24hrs. The suggested baking conditions are as followings:

- 60±5°C x 12~24hrs and <5%RH, taped / reel package.

It's normal to see slight color fading of carrier (light yellow) after baking in process.

Testing Circuit:



Must apply resistor(s) for protection (over current proof).

Cleaning:

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED carrier / package. Avoid putting any stress force directly on to the LED lens.

ESD (Electrostatic Discharge):

Static Electricity or power surge will damage the LED. Use of a conductive wrist band or anti-electrostatic glove is recommended when handling the LED all time. All devices, equipment, machinery, work tables, and storage racks must be properly grounded.

In the events of manual working in process, make sure the devices are well protected from ESD at any time.

REVISION RECORD:

Version	Date	Summary of Revision
A1.0	25/06/2026	Datasheet set-up.