




Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten.

General Information:

- Simplified representation, exemplary shown in gray.
- Document excluded from change process
- Units are in millimeters [mm] and degrees [°]
- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
- Workpiece zero point for mechanical processing
- Tolerances for mechanical processing are ISO 2768-mk
- Tolerances for printing DIN ISO 2768-m
- Machining radii min. R1, further on request
- Web: www.phoenixcontact.com webcode: #0308

Additional Information:

A. Printing area, consider edge radii 0,2
B. Machining area, for mechanical processing
C. Bottom side
D. PCB position (t=1,5)
E. Guidance between Cover and Housing
F. Latching point between Cover and Housing
G. Display 2,4", for further information see article 1132710

Pos.	QTY	Description	Material		
1	1	COVER	PA		
2	1	DISPLAY			
 DIN A2		document-No. / RI 01313669 / 01		date 06.05.2025	scale 1:1
		ident.-No. 1225275		document-type TECDOC 2D_Productdrawing	
		description ME-IO 56,4 C 10U D2,4-TRG 7035-VPE1			
		page 1		of 1	