




VOLTAGE RANGE: 1200 --- 2000 V
CURRENT: 0.5 A

Features

- Low cost
- Diffused junction
- Low leakage
- Low forward voltage drop
- High current capability
- Easily cleaned with Freon, Alcohol, Isopropanol and similar solvents
- The plastic material carries U/L recognition 94V-0

DO - 41



Mechanical Data

- Case: JEDEC DO-41, molded plastic
- Polarity: Color band denotes cathode
- Weight: 0.339 grams
- Mounting position: Any

Dimensions in millimeters

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.

		RGP02 -12E	RGP02 -14E	RGP02 -16E	RGP02 -18E	RGP02 -20E	UNITS
Maximum recurrent peak reverse voltage	V_{RRM}	1200	1400	1600	1800	2000	V
Maximum RMS voltage	V_{RMS}	840	980	1120	1260	1400	V
Maximum DC blocking voltage	V_{DC}	1200	1400	1600	1800	2000	V
Maximum average forward rectified current 9.5mm lead lengths, @ $T_A=75$	I_{AV}	0.5					A
Peak forward surge current 8.3ms single half-sine-wave superimposed on rated load @ $T_J=125$	I_{FSM}	20					A
Maximum instantaneous forward voltage at 0.1 A	V_F	1.8					V
Maximum reverse current @ $T_A=25$ at rated DC blocking voltage @ $T_A=100$	I_R	5.0 50					μA
Maximum reverse recovery time (Note1)	t_{rr}	300					ns
Typical junction capacitance (Note2)	C_J	5					pF
Typical thermal resistance (Note3)	$R_{\theta JA}$	80					/W
Operating junction temperature range	T_J	- 65 ---- +150					
Storage temperature range	T_{STG}	- 65 ---- + 150					

NOTE: 1. Measured with $I_F=0.5A$, $I_R=1A$, $I_{rr}=0.25A$.

2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

3. Thermal resistance from junction to ambient.

Ratings AND Characteristic Curves

FIG.1 – REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM




FIG.2 –DERATING CURVE FOR OUTPUT RECTIFIED CURRENT




FIG.3 –MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.4-TYPICAL FORWARD CHARACTERISTIC





FIG.5-TYPICAL REVERSE CHARACTERISTICS



PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
DO-41	5000/AMMO	50000	42X28X31	14.00	12.00