

# PRO HOLDER Ball joint holder

**Art.-No.**
**KGH60-KG-IGM8**
**Description**

ball Ø 60 mm (max. 140kg) Internal thread M8

**Features**

Connection M8 × 1.25 (6h) L = 10.5 mm

Torque up to 100 Nm, holding force up to 140 kg

Mounting surface Ø 36 mm, incl. rotation prevention by 2 × M5 thread

Counterface SW22

Tilt angle ball +/- 45°

Clamping base for table tops max. 80 mm

Cast aluminum, powder coated (gray anthracite)

Made in Germany

Orientation dimensions (HxWxD) 241 × 152 × 152 mm

Weight 2789 g


**Application and technical data**

Strong holding force with pinpoint clamping. The ball can be fixed in any position via the black lever. All devices can be screwed onto the thread and ideally aligned. Available are internal and external threads in M6, M8, M12 or UNC 1/4 inch. With an additional adapter of 45 degrees, 90 degree inclination can be achieved. A small lever pressure is sufficient for a stepless fixing with high holding force. With the adjusting screw on the lower seat of the ball, the movement of the ball can be adjusted from loose to very firm. For safety-relevant parts, please note that we cannot give a guarantee of the holding forces without knowing your specific application. The ball may behave differently under different physical conditions than it does in our test laboratory in an optimal test environment. Our product development department is constantly working on the optimisation and further development of our products. If you have any questions, improvements or suggestions, we look forward to hearing from you.

**Detail drawing**
