

Heavy Duty 72 Teeth Adjustable Torque Wrench

Colorful quick release button design

Fixed head version allows using in narrow spaces

Quality accords to DIN ISO 6789:2017 & ASME B107.300-2010

Tolerance of torque $\pm 3\%$ (CW)

CW/CCW Direction



Single scale - Newton Meter (N-m)

KT NO.	Square drive	Torque range N-m	Incr.	Overall length mm		
3426A-1DG	1/4"	2~10 N-m	0.1 N-m	285	560	1 / 24
3426A-2DG	1/4"	4~20 N-m	0.1 N-m	325	640	1 / 24
3436A-2DG	3/8"	20~100 N-m	0.5 N-m	430	1300	1 / 12
3446A-1DG	1/2"	40~200 N-m	1 N-m	490	1460	1 / 12
3446A-2DG	1/2"	60~340 N-m	2 N-m	590	1750	1 / 12

Single scale - English (in-lb/ft-lb)

KT NO.	Square drive	Torque range in-lb / ft-lb	Incr.	Overall length mm		
3426A-1EG	1/4"	20~100 in-lb	1 in-lb	285	560	1 / 24
3426A-2EG	1/4"	40~200 in-lb	1 in-lb	325	640	1 / 24
3436A-2EG	3/8"	15~80 ft-lb	0.5 ft-lb	430	1300	1 / 12
3446A-1EG	1/2"	20~150 ft-lb	1 ft-lb	490	1460	1 / 12
3446A-2EG	1/2"	50~250 ft-lb	1 ft-lb	590	1750	1 / 12



- 3426A-1DK
 - 3436A-2DK
 - 3446A-1DK
- series No. before 17086A



- 3426A-1DK01
 - 3436A-2DK01
 - 3446A-1DK01
- series No. after 17086A



- 3426A-1DK02
 - 3436A-2DK02
 - 3446A-1DK02
- series No. after 19106A

