



Harmony XVB7

Modular tower lights
Signaling units Ø 70



Harmony

Discover [Harmony](#)

Advanced operator interface and industrial relays

Harmony operator interface and industrial relays enhance operational efficiency and equipment availability across industrial and building applications. **Harmony** includes intelligent connected products and edge terminals that visualize, gather and process data, enabling informed operator decisions

Explore our offer

- [Harmony](#) Push Buttons and Switches
- [Harmony](#) HMI Operator Terminals, IPC and EdgeBox
- [Harmony](#) Signaling Devices
- [Harmony](#) Electrical Relays
- [Harmony](#) Safety

Life Is On

Schneider
Electric

Quick access to product information

Get technical information about your product


References

Modicon TM3
I/O expansion modules for Modicon controllers
Analog I/O modules


Reference	Input range	Output range	Resolution	Input terminal block (T)	Reference	Weight (kg)
2 voltage/current inputs	-15...+15 VDC 0...+10 VDC 0...20 mA A...20 mA	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	TM3AI2H	0.150
4 voltage/current inputs	-15...+15 VDC 0...+10 VDC 0...20 mA A...20 mA	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	TM3AI4H	0.200
4 voltage/current or temperature inputs (T)	Thermocouples (T) J, K, R, S, E, T, N, B, C Temperature inputs (I) PT100, PT500, RTD, ITC100, ITC500	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	TM3AI4H	0.200
4 differential temperature inputs	Thermocouples (T) J, K, R, S, E, T, N, B, C Temperature inputs (I) PT100, PT500, RTD, ITC100, ITC500	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	TM3AI4H	0.200
4 differential temperature inputs	Thermocouples (T) J, K, R, S, E, T, N, B, C Temperature inputs (I) PT100, PT500, RTD, ITC100, ITC500	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	10 000 01 10 000 01 10 000 01	TM3AI4H	0.200

Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:


- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Product image, Instruction sheet, User guide, Product certifications, End of life manual



Find your catalog



- > With just 3 clicks, you can access the Industrial Automation and Control catalogs, in both English and French
- > Consult digital automation catalogs at [Digi-Cat Online](#)




- Up-to-date catalogs
- Embedded product selectors, 360° pictures
- Optimized search by commercial references

Select your training



- > Find the right [Training](#) for your needs on our Global website
- > Locate the training center with the selector tool, using this [link](#)



Life Is On

Schneider
Electric

General contents

Harmony® XVB7 modular tower lights Ø 70 mm

- Selection guide** page 2
- Presentation, selection, and description**
 - Modular tower lights for customer assembly page 6
 - How to select your Harmony modular tower light page 7
 - Construction overview page 8
- References**
 - Base modules page 10
 - Light modules with steady light signal page 11
 - Light modules with blinking light signal page 11
 - Light modules with flashing light signal page 11
 - Rotating modules page 12
 - Multi-functional module page 12
 - Beacon lens with steady light signal page 12
 - Beacon lens with flashing light signal page 12
 - Audible modules page 13
 - Mounting accessories page 14
- Product reference index** page 15

Harmony XV

Monolithic tower lights



Type of products		Pre-assembled and pre-cabled USB tower lights	Pre-assembled/pre-cabled tower lights Modular tower lights for customer assembly of up to 4 units
Diameter		Ø 60 mm/2.362 in.	Ø 60 mm/2.362 in.
Degree of protection conforming to IEC 60529		IP 54	IP 53 and IP 42 (base mounting) IP 23 (direct aluminium tube mounting, aluminium tube mounting and "L" bracket) IP 53 and IP 42 (aluminium tube mounting and fixing plate) IP 40 (aluminium tube mounting and foldable bracket)
Type of signalling	Steady	Yes	Yes
	Flashing	Yes	—
	High flashing	—	—
	Sound	With buzzer (volume control and alarm type can be set with HMI)	With buzzer
Light sources	Incandescent bulb	—	—
	LED bulb	—	—
	Integral LED	Yes	Yes
	"Flash" discharge tube	—	—
	Halogen bulb	—	—
Colors of illuminated units		Mutli-color LEDs (many possible combinations can be set with HMI) ☐ Red ☐ Orange ☐ Green ☐ Blue	☐ Red ☐ Green ☐ Amber ☐ Blue
Connection		USB power cable: - 300 mm/11.81 in. for tube mounting - 400 mm/15.75 in. for direct mounting	Flying leads, length 500 to 560 mm/19.68 to 22.05 in. for tube mounting according to model. Length 900 mm/35.43 in. for base mounting.
Mounting options		Mounting on support tube with fixing plate: 4 x Ø 6 mm/0.236 in. Direct mounting on horizontal support: 3 x Ø 5 mm/0.197 in.	Base mounting: 3 x Ø 5 mm/0.197 in. Direct aluminium tube mounting: Ø20/0.787 in. Aluminium tube mounting and "L" bracket: 2 x Ø9/0.354 in. Aluminium tube mounting and fixing plate: 4 x Ø6/0.236 in. Aluminium tube mounting and foldable bracket: 4 x Ø6/0.236 in.
Type references		XVGU	XVG

Monolithic tower lights



Pre-assembled and pre-cabled tower lights		Pre-assembled and pre-cabled tower lights		Pre-assembled and pre-cabled tower lights	
Diameter		Ø 40 mm/1.575 in.	Ø 60 mm/2.36 in.	Ø 100 mm/3.937 in.	
Degree of protection conforming to IEC 60529		IP 54 (flat surface installation) IP 23 (vertical surface installation)	IP 54 (flat surface installation) IP 23 (vertical surface installation)	IP 54 (flat surface installation)	
Type of signalling	Yes	Yes	Yes	Yes	
	Yes	Yes	Yes	Yes	
	—	—	—	—	
	With buzzer	With buzzer	With buzzer	With siren or buzzer	
Light sources	—	—	—	—	
	—	—	—	—	
	Yes	Yes	Yes	Yes	
	—	—	—	—	
	—	—	—	—	
Colors of illuminated units		☐ Red ☐ Orange ☐ Green ☐ Blue ☐ White	☐ Red ☐ Orange ☐ Green ☐ Blue ☐ White	☐ Red ☐ Orange ☐ Green ☐ Blue ☐ White	
Connection		Flying leads, length 450 mm/17.71 in. to 900 mm/35.43 in. according to model	Flying leads, length 450 mm/17.71 in. to 850 mm/33.46 in. according to model	Flying leads, length 500 mm/19.68 in.	
Mounting options		Mounting on support tube with bracket: 2 x Ø 9 mm/0.354 in. Direct mounting on horizontal support: 3 x Ø 5 mm/0.20 in. Other mounting possibilities with accessories	Mounting on support tube with bracket: 2 x Ø 11 mm/0.43 in. Direct mounting on horizontal support: 3 x Ø 5 mm/0.197 in. Other mounting possibilities with accessories	Direct mounting on horizontal support: - 3 x Ø 6 mm/0.236 in. (without siren) - 3 x Ø 7 mm/0.276 in. (with siren) Other mounting possibilities with accessories	
Type references		XVC4	XVC6	XVC1	



Harmony XV		Modular tower lights	
			
Type of products		Illuminated beacons Modular tower lights for customer assembly of up to 5 units	Tower lights for customer assembly of up to 5 units
Diameter		Ø 70 mm/2.756 in.	Ø 60 mm/2.362 in.
Degree of protection conforming to IEC 60529		IP65 (mounted on fixing base XVZ●●) IP66 (mounted on base module)	IP65 for illuminated units IP54 for audible units IP55 for flexible mounting unit
Type of signalling	Steady	Yes	Yes
	Blinking	Yes	Yes
	Flashing	Yes	Yes
	High flashing	–	Yes
	“Flash”	Yes	–
	Sound	Yes (buzzer or editable voice)	Yes (buzzer or editable voice)
Light sources	Incandescent bulb	–	–
	LED bulb	–	–
	Integral LED	Energy-efficient LED	Yes
	“Flash” discharge tube	–	–
	Halogen bulb	–	–
Colors of illuminated units		☐ Green ☐ Red ☐ Orange ☐ Blue ☐ White ☐ Yellow	☐ Green ☐ Red ☐ Orange ☐ Blue ☐ White ☐ Yellow
Connection		Push-in terminals, M12 or USB connector, depending on model	Spring cage connection terminals
Mounting options		1/2" NPT adapter Plastic fixing plate with tube L bracket aluminium tube Plastic foldable bracket Plastic wall mount bracket Side entry adapter Magnetic adapter	Mounting on support tube and adjustable support tube: 4 x Ø 6 mm/0.236 in. Flexible wall mounting: 3 x Ø 5 mm/0.197 in. Direct mounting: 2 x Ø 5 mm/0.197 in. 3 x Ø 5 mm/0.197 in. 4 x Ø 5 mm/0.197 in. Mounting on bracket: 2 x Ø 9 mm/0.354 in.
Type references		XVB7	XVU

Modular tower lights	Rotating beacons	Beacons	Sound solutions
			
Pre-assembled/pre-cabled tower lights Variable composition tower lights for customer assembly of up to 5 units	Pre-cabled rotating beacons Pre-cabled motor-less rotating/flashing beacons	Complete miniature beacons	Sirens and electronic alarms
Ø 45 mm/1.772 in.	Ø 84 mm/3.31 in. to Ø 130 mm/5.12 in.	Ø 45 mm/1.772 in.	–
IP 54 in vertical position (XVM with plastic fixing plate) IP 42 in horizontal position (XVM with metal bracket) IP 40 in other positions (all types of XVM tower lights)	Ø 84 mm/3.31 in. and Ø 106 mm/4.17 in.: IP 23 (IP 65 with accessory) Ø 120 mm/4.72 in.: IP 23 Ø 130 mm/5.12 in.: IP 66 and IP 67 (depending on voltage) Ø 100 mm/3.94 in.: IP 65 for upright position, IP 23 for sideways and inverted position	IP 40	IP 53 (sirens) IP 54 (electronic alarms) IP 65 (editable voice)
Yes	Yes	Yes	–
–	Yes	–	–
Yes	–	–	–
–	–	–	–
Yes	–	Yes	–
Yes	Yes	–	Yes (editable voice)
Yes	–	Yes	–
Yes	“Super Bright”	–	–
–	–	–	–
Yes	–	Yes	–
–	Yes	–	–
☐ Red ☐ Green ☐ Orange ☐ Blue ☐ White	☐ Red ☐ Orange ☐ Green ☐ Blue	☐ Green ☐ Red ☐ Orange ☐ Blue ☐ White ☐ Yellow	–
Flying leads, length 300 mm/11.81 in. or screw terminals	Flying leads, length 400 mm/15.75 in. (except XVR08: 500 mm/19.68 in.)	Screw clamp terminals	Screw clamp terminals (except XVS14: flying leads, length 500 mm/19.68 in.)
Mounting on bracket: 2 x Ø 9 mm/0.354 in. Mounting on support tube: 4 x Ø 5.5 mm/0.217 in. or M5	Depending on model: – XVR08 (Ø 84 mm/3.31 in.): 3 x Ø 5 mm/0.197 in. – XVR10 (Ø 106 mm/4.17 in.): 3 x Ø 5 mm/0.197 in. – XVR12 (Ø 120 mm/4.72 in.): 3 x Ø 6 mm/0.236 in. – XVR13 (Ø 130 mm/5.12 in.): 3 x Ø 9 mm/0.354 in. – XVR13●●●L (Ø 130 mm/5.12 in.): 3 x Ø 7 mm/0.276 in. – XVR3 (Ø 100 mm/3.94 in.): 3 x Ø 6 mm/0.236 in.	3 x Ø 3.3 mm/0.130 in. or M3	3 x Ø 6.5 mm/0.256 in.
XVM	XVR	XVDLS	XVS

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)


Harmony XVB7:

- Tower lights Ø 70 mm for customer assembly with light and sound functions




Diamond-cut lens for even light

EcoStruxure Operator Terminal Expert



Connectivity with Modbus protocol



Connectivity with IO-Link protocol

Harmony XVB7: redefining signaling excellence

The beacons and tower lights of the Harmony XVB7 range are visual or audible signaling units used for indicating, throughout 360° and at a distance, the various states or operation sequences of a machine or installation.

Examples: start, stop machine, no material, call technical staff, fault signaling, etc.

- > Harmony Modular Tower Lights, **launching in 2025**, feature a sleek, new design incorporating universal LEDs to maximize brightness while minimizing energy consumption.
- > With easy installation and a modular concept, Harmony Modular Tower Lights simplify your selection journey and enable operational efficiency.
- > These enhancements minimize the quantity of references that need to be stocked by end users, OEMs, and distributors, thereby optimizing supply chains and ensuring availability at the right place and time.

Brilliant, Connected, and Streamlined for your success!

Flexible

- > **Modular** concept provides flexibility in the selection
- > **IO-Link** and **Modbus over USB** connections to enable more operation capability

Efficient

- > More **rationalized construction** that reduces SKUs by 3X while maintaining the same functional coverage (1)
- > Reduce wiring time up to 95% with **push-in terminals** and **M12** connection
- > Power optimization via **energy-efficient LED**

Aesthetic

- > Elevated **Modern Design**
- > Available in both **dark grey** and **silver** body color

Visible, audible

- > 4X improvement in **brightness**
- > Audible signal **up to 102dB**

Service and availability

- > Supported by Schneider Electric service
- > Wide availability throughout an extensive distribution network

(1) SKUs: Stock-Keeping Units.

+ Energy efficiency LEDs while achieving greater brightness

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)



How to select your Harmony modular tower light

Step 1: base module selection

- > The base module determines the voltage level of the complete tower light
- > Different types of connection are available:
 - IO-Link base enables direct plug and play into IO-Link solution with ready IODD file
 - USB base integrated with Schneider Electric HMI as a solution offer
 - ~/- 24 V base with M12 connector maximizes wiring efficiency

Step 2: lens or light module selection

- > Maximum of 5 layers, including the top module
- > All light modules operate with a 24 V supply voltage
- > Choose from 6 colors and 4 light patterns

Step 3: top module selection

- > Top module can be either a sounder, a beacon, or a cover
- > All audible modules and beacons operate with a 24 V supply voltage
- > Sound buzzers are adjustable up to 102 dB with 2-tone or 8-tone pattern (IP66) or as a self adjustable buzzer (IP65) that adapts automatically based on ambient noise up to 100 dB
- > The editable sounder can be programmed up to 16 tones and supports MP3/Wav files.

Step 4: mounting accessory selection

- > Universal accessories, common across all diameter of 70 mm, 60 mm, and 40 mm.
- > Available in various tube lengths ranging from 100 mm to 800 mm
- > Includes various types of mounting options

Choose the base module (see page 10)

Determines the overall voltage of the product

Example	X	V	B	7	C	21B	Q
Base module for direct fixing	X	V	B	7	C		
Voltage/ type	~/- 24 V base					21B	
	~ 100-240 V base					21M	
	IO-Link base					31	
	USB base via Modbus protocol					51	
	~/- 24 V, M12 quick connection base					61	
Color	Silver						Q
	Dark grey						(1)

Choose the light module (see pages 11 and 12)

All 24 V, can stack up to 5 layers, including beacon and audible module

Example	X	V	B	7	C	2	5
Base module for direct fixing	X	V	B	7	C		
Type	Steady light					2	
	Blinking light					5	
	Flashing light					6	
	Rotating light (only red or orange)					R	
	Multi-function					M	
Color	Green						3
	Red						4
	Orange						5
	Blue						6
	White						7
	Yellow						8
	Multi-colored						9

(1) No character or digit for dark grey


Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Construction overview



Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Construction overview

Construction overview

Customer assembled tower lights Harmony XVB7

Variable composition of 1 to 5 light or audible modules that are supplied as separate items for customer assembly.

Maximum configuration:

- 5 units (24 V, IO -Link, USB base)
- 4 units (M12, AC base)

The **Harmony XVB7** range comprises:

- 5 base modules with push-in terminals or M12 quick connection 5:
(top cover 1 included, side cable entry adapter 15 can be purchased separately).
 - ~ 24 V, push-in terminals (dark grey or silver)
 - ~ 100...240 V, push-in terminals (dark grey or silver)
 - ~ 24 V, M12 connection (dark grey)
 - USB over modbus protocol, USB connection (dark grey)
 - IO-Link protocol, M12 connection (dark grey)
- 21 colored light modules 4:
 - 6 with steady light signal (green, red, orange, blue, white or yellow)
 - 6 with blinking light signal (green, red, orange, blue, white or yellow)
 - 6 with flashing light signal (green, red, orange, blue, white or yellow)
 - 2 rotating modules (red and orange)
 - 1 multi-functional module (clear lens, 8 colors, 4 light patterns)
- 12 beacon lens 3:
 - 6 with steady light signal (green, red, orange, blue, white or yellow)
 - 6 with flashing light signal (green, red, orange, blue, white or yellow)
- 4 audible modules 2
 - 2 tones buzzers (dark grey or silver)
 - 8 tones buzzers (dark grey)
 - Self adjust buzzer
 - Customizable vocal element
- A maximum of one beacon 3 or sound module 2, for mounting on top of the bank
- Top cover 1 (provided with each base module).
- The light or audible modules stack vertically and are easily locked and unlocked using an integral clamping ring. Electrical connections between each unit are made automatically.

Mounting options

- Wall mounting bracket 6.
- 1/2" NPT adaptor 7.
- Fixing plates with tube mounting 8.
- Ø 25 mm aluminium tubes, height 100, 250, 400 or 800 mm 9.
- L brackets for Ø 25 mm aluminium tubes (height 100 or 250 mm) 10.
- Fixing plates for tube mounting (metal 11 or plastic 12).
- Foldable brackets 13.
- Side cable entry adaptor 14.
- Magnetic adaptor 15.

Cabling

By means of removable push-in terminal block incorporated in base module (simplified wiring).

Signaling units
Modular tower lights Ø 70 mm
Harmony® XVB7
Tower lights for customer assembly (up to 5 units)
Base modules




XVB7C21B



XVB7C21BQ



XVB7C21M



XVB7C21MQ

Base modules for direct fixing (IP66) or tube fixing (IP65)

Description	Voltage Connection	Color	Reference	Weight kg/lb
Standard base modules with tube and cover	~ 24 V Push-in terminals	Dark grey	XVB7C21B	0.164/ 0.361

Silver	XVB7C21BQ ▲	0.165/ 0.363
--------	--------------------	-----------------

24 V M12 connector (A-coded, 15 cm cable)	Dark grey	XVB7C61	0.289/ 0.637
---	-----------	----------------	-----------------

100 - 240 V 120 V Push-in terminals	Dark grey	XVB7C21M	0.280/ 0.617
---	-----------	-----------------	-----------------

Silver	XVB7C21MQ ▲	0.282/ 0.621
--------	--------------------	-----------------

IO-Link



XVB7C31



XVB7C61

Connected base modules with tube, cover and wiring pull-out protection	5 V Modbus protocol USB 2.0 Type C connection (cable not included)	Dark grey	XVB7C51 ▲	0.180/ 0.397
--	---	-----------	------------------	-----------------

24 V IO-Link protocol (V1.1) M12 connector (A-coded, 15 cm cable)	Dark grey	XVB7C31	0.227/ 0.500
--	-----------	----------------	-----------------

▲ : Available 2nd semester 2025.

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Light modules



XVB7C23



XVB7C24



XVB7C25



XVB7C26



XVB7C27



XVB7C28




XVB7C53



XVB7C54



XVB7C55



XVB7C56



XVB7C57



XVB7C58




XVB7C63



XVB7C64



XVB7C65



XVB7C66



XVB7C67



XVB7C68

Light modules with steady light signal (IP66)

Description	Light source	Color	Reference	Weight kg/lb
Light modules with energy-efficient LED	LED, included ~24 V	Green	XVB7C23	0.105/ 0.231
		Red	XVB7C24	0.105/ 0.231
		Orange	XVB7C25	0.105/ 0.231
		Blue	XVB7C26	0.105/ 0.231
		White	XVB7C27	0.105/ 0.231
		Yellow	XVB7C28	0.105/ 0.231

Light modules with blinking light signal (IP66)

Description	Light source	Color	Reference	Weight kg/lb
Light modules with energy-efficient LED	LED, included ~24 V	Green	XVB7C53	0.105/ 0.231
		Red	XVB7C54	0.105/ 0.231
		Orange	XVB7C55	0.105/ 0.231
		Blue	XVB7C56	0.105/ 0.231
		White	XVB7C57	0.105/ 0.231
		Yellow	XVB7C58	0.105/ 0.231

Light modules with flashing light signal (IP66)

Description	Light source	Color	Reference	Weight kg/lb
Light modules with energy-efficient LED	LED, included ~24 V 2 Joules flash	Green	XVB7C63	0.108/ 0.238
		Red	XVB7C64	0.108/ 0.238
		Orange	XVB7C65	0.108/ 0.238
		Blue	XVB7C66	0.108/ 0.238
		White	XVB7C67	0.108/ 0.238
		Yellow	XVB7C68	0.108/ 0.238

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Rotating and multi-functional modules. Beacon lens



XVB7CR4



XVB7CR5



XVB7CM9



XVB7L23



XVB7L24



XVB7L25




XVB7L26



XVB7L27



XVB7L28



XVB7L63



XVB7L64



XVB7L65



XVB7L66



XVB7L67



XVB7L68

Rotating and multi-functional modules (IP66)

Description	Light source	Color	Reference	Weight kg/lb
Rotating modules	LED, included ~ 24 V	Red	XVB7CR4 ▲	0.107/ 0.233
		Orange	XVB7CR5 ▲	0.106/ 0.233

Multi-functional module adjustable via dip switch: - 8 colors, 4 light patterns - Steady, blinking, 2 x flash, 3 x flash	LED, included ~ 24 V	Clear lens 8 colors (blue, green, orange, red, white, yellow, turquoise and violet)	XVB7CM9	0.107/ 0.235
---	-------------------------	--	----------------	-----------------

Beacon lens with steady light signal (IP66)

Description	Light source	Color of lens	Reference	Weight kg/lb
Beacon lens	LED, included ~ 24 V	Green	XVB7L23	0.094/ 0.207
		Red	XVB7L24	0.094/ 0.207
		Orange	XVB7L25	0.094/ 0.207
		Blue	XVB7L26	0.094/ 0.207
		White	XVB7L27	0.094/ 0.207
		Yellow	XVB7L28	0.094/ 0.207

Beacon lens with flashing light signal (IP66)

Description	Light source	Color of lens	Reference	Weight kg/lb
Beacon lens	LED, included ~ 24 V 2 Joules flash	Green	XVB7L63	0.108/ 0.238
		Red	XVB7L64	0.108/ 0.238
		Orange	XVB7L65	0.108/ 0.238
		Blue	XVB7L66	0.108/ 0.238
		White	XVB7L67	0.108/ 0.238
		Yellow	XVB7L68	0.108/ 0.238

▲ : Available 2nd semester 2025.


Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Audible modules



XVB7C9S



XVB7C9SQ



XVB7C9V

Audible modules

Description	Sound pattern	Color	Reference	Weight kg/lb
Sounder - 360° omni sound - IP66 - Up to 102 dB (A) at 1 meter - Voltage: ~/- 24 V	2 tones buzzer (continuous or intermittent)	Dark grey	XVB7C9S	0.080/ 0.176
		Silver	XVB7C9SQ ▲	0.081/ 0.178
	8 tones buzzer (continuous or intermittent)	Dark grey	XVB7C9T ▲	0.081/ 0.178
Self adjust sounder - Sound pressure adjust automatically based on ambient sound - IP65 - 80 to 100 dB (A) at 1 meter - Voltage: ~/- 24 V	1 tone buzzer (intermittent)	Dark grey	XVB7C9SS ▲	0.080/ 0.176
Customizable sounder/voice alarm - Type C USB for programming - IP65 - Maximum 16 tones (8 MB memory) - 88 dB (A) at 1 meter - Supports MP3/Wav files - Voltage: - 24 V	Vocal	Dark grey	XVB7C9V ▲	0.212/ 0.467

▲ : Available 2nd semester 2025.

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Mounting accessories

Fixing plates


Fixing plates without tube

Description	Material	Color	Reference	Weight kg/lb
Fixing plates for base mounting - IP66 (metal) - IP65 (plastic) - Bottom cable entry - Gasket and screws included	Plastic	Dark grey	XVZ01	0.042/ 0.092
		Silver	XVZ01Q ▲	0.042/ 0.092
		White	XVZ01W ▲	0.042/ 0.092
	Metal	Black	XVZ11	0.117/ 0.257




Fixing plates with tube

Description	Height mm/in.	Material	Color	Reference	Weight kg/lb
Plastic fixing plates comprising a Ø 25 mm tube - IP66 - Bottom cable entry - Gasket and screws included	100/ 3.94	Plastic	Dark grey	XVZ02	0.081/ 0.178
			Silver	XVZ02Q	0.081/ 0.178



Tubes

Description	Height mm/in.	Material	Color	Reference	Weight kg/lb
Aluminium tubes Ø 25 mm - IP66 - Bottom cable entry	100/ 3.94	Aluminium	Silver	XVZ100	0.040/ 0.088
	250/ 9.84	Aluminium	Silver	XVZ250	0.098/ 0.216
	400/ 15.75	Aluminium	Silver	XVZ400	0.156/ 0.343
	800/ 31.50	Aluminium	Silver	XVZ800	0.311/ 0.685



▲ : Available 2nd semester 2025.

Signaling units

Modular tower lights Ø 70 mm

Harmony® XVB7

Tower lights for customer assembly (up to 5 units)

Mounting accessories



XVZ100T



XVZ06



XVZ06W



XVZ09



XVZ00



XVZ07



XVZ08

Fixing L brackets with integrated tube

Description	Height of tube mm/in.	Material	Color	Reference	Weight kg/lb
Steel L brackets comprising a Ø 25 mm aluminium tube - IP23 - Bottom cable entry	100/ 3.98	Aluminium (tube) Steel (bracket)	Silver	XVZ100T	0.332/ 0.732
	250/ 9.84	Aluminium (tube) Steel (bracket)	Silver	XVZ250T	0.381/ 0.840

Brackets

Description	Material	Color	Reference	Weight kg/lb
Foldable brackets for mounting at various angles - IP40 - Bottom cable entry - Screws included	Plastic	Dark grey	XVZ06	0.123/ 0.271
		White	XVZ06W	0.123/ 0.271

Wall mounting bracket for use on vertical support - can be combined with L brackets XVZ100T and XVZ250T - IP66 - Screws included	Plastic	Dark grey	XVZ09	0.050/ 0.110
---	---------	-----------	--------------	-----------------

Other mounting accessories

Description	Material	Color	Reference	Weight kg/lb
1/2" NPT adapter - IP66 - Bottom cable entry	Steel	Silver	XVZ00	0.101/ 0.222
Side cable entry adapter for base mounting (M16 x 1.5 cable gland) - IP65 - Gasket and screws included	Plastic	Dark grey	XVZ07	0.069/ 0.152
Magnetic adapter for base mounting with side cable entry (M16 x 1.5 cable gland) - IP65 - Screws included	Plastic	Dark grey	XVZ08	0.298/ 0.657

X		XVZ100	14
XVB7C21B	10	XVZ100T	15
XVB7C21BQ	10	XVZ11	14
XVB7C21M	10	XVZ250	14
XVB7C21MQ	10	XVZ250T	15
XVB7C23	11	XVZ400	14
XVB7C24	11	XVZ800	14
XVB7C25	11		
XVB7C26	11		
XVB7C27	11		
XVB7C28	11		
XVB7C31	10		
XVB7C51	10		
XVB7C53	11		
XVB7C54	11		
XVB7C55	11		
XVB7C56	11		
XVB7C57	11		
XVB7C58	11		
XVB7C61	10		
XVB7C63	11		
XVB7C64	11		
XVB7C65	11		
XVB7C66	11		
XVB7C67	11		
XVB7C68	11		
XVB7C9S	13		
XVB7C9SQ	13		
XVB7C9SS	13		
XVB7C9T	13		
XVB7C9V	13		
XVB7CM9	12		
XVB7CR4	12		
XVB7CR5	12		
XVB7L23	12		
XVB7L24	12		
XVB7L25	12		
XVB7L26	12		
XVB7L27	12		
XVB7L28	12		
XVB7L63	12		
XVB7L64	12		
XVB7L65	12		
XVB7L66	12		
XVB7L67	12		
XVB7L68	12		
XVZ00	15		
XVZ01	14		
XVZ01Q	14		
XVZ01W	14		
XVZ02	14		
XVZ02Q	14		
XVZ06	15		
XVZ06W	15		
XVZ07	15		
XVZ08	15		
XVZ09	15		

mySchneider, your personalized digital experience

Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- **Efficiency:** In just a few clicks, find all the information and support you need to get the job done.
- **Simplicity:** Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- **Personalization:** Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

Watch the How-to Videos



Order management

- > [Select Products and Add to Cart](#)
- > [Check for Products' Price and Availability](#)
- > [Order Products with Generic Commercial References](#)




Product information

- > [Find a Product Data Sheet and Related Documents](#)
- > [Select Products and Add to Cart](#)
- > [Stay Up to Date on the Status of My Products](#)



Support

- > [Get Quicker Answers Thanks to Online Support](#)



Training

- > [Access Trainings Dedicated to My Activity](#)

[Create your account](#)

Life Is On

Schneider
Electric

Legal information

The information provided in this Catalog contains description of Schneider Electric products, solutions and services ("Offer") with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any type of damages arising out of or in connection with (i) informational content of this Catalog not conforming with or exceeding the technical specifications, or (ii) any error contained in this Catalog, or (iii) any use, decision, act or omission made or taken on basis of or in reliance on any information contained or referred to in this Catalog.


SCHNEIDER ELECTRIC MAKES NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOG OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS AND SERVICES WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Schneider Electric brand and any trademarks of Schneider Electric and its subsidiaries referred to in this Catalog are property of Schneider Electric or its subsidiaries. All other brands are trademarks of their respective owners.

This Catalog and its content are protected under applicable copyright laws and provided for informative use only. No part of this Catalog may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Copyright, intellectual, and all other proprietary rights in the content of this Catalog (including but not limited to software, audio, video, text, and photographs) rests with Schneider Electric or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.

Life Is On



Learn more about our products at www.se.com

Design: Schneider Electric
Photos: Schneider Electric

Schneider Electric Industries SAS

Head Office
35, rue Joseph Monier - CS 30323
F-92500 Rueil-Malmaison Cedex
France

DIA5ED2241101EN
April 2025 - V1.0