




SUGGESTED PANEL CUTOUT

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	OFF	ON
2-3	OPEN	1-2





CIRCUIT: SPDT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 15A @125VAC [cURus]
5. MATERIAL:
CONTACT SURFACE: SILVER PLATED COPPER
CIRCUIT TERMINAL: BRASS ALLOY w/SILVER PLATE
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. CONTACT RESISTANCE: 20 mΩ MAX.
8. INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC
9. OPERATING TEMP: -20°C to 105°C [cURus]
10. DIELECTRIC STRENGTH: >1,000V AC 1MIN
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LAMP VOLTAGE: NON-ILLUMINATED



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
F	ECO-101466	UPDATED PRINT	12/15/22	JS						000001615
					TITLE RSC145C1100					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV	
					3:2	11/4/2010	CAB	38-RSC145C1100	F	