


Dept / Qty	
DC	1
ED	1
IE	1
ISO	1
PD	1
R&D	1
SD	1
QA	1
QC	1
QE	1

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 04/14/26'		







Recommend PCB Layout
Tolerance=±0.05

NOTE:

1. Materials:
   1.1 Base: Thermoplastic,UL94 V-0,Color of black.
   Temp.Range: -25°C to +85°C.
   1.2 Positive & Negative Contacts: Copper Alloy.
2. Specification:
   2.1 Dielectric Withstanding Voltage: AC 500V AC.
   2.2 Insulation Resistance: 1000MΩ min.
   2.3 Contact Resistance: 100mΩ Max.
3. Part Number Code:
   DS1092-04 - X X X - 01
   - Housing material: P: PBT
   - Contact plating: N: Nickel
   - Housing color: B: Black



(Series Image-Reference Only)

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1092-04-BNP-01-A		

PROJECTION		TITLE	2032 Lithium Coin Cell Battery Holders Horizontal insert type
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1092-04 SERIES

CONNFLY 晨翔电子有限公司
CONNFLY ELECTRONIC CO. LTD

The information provided herein is from CONNFLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNFLY or its affiliates. Unauthorized use or modification is strictly prohibited without prior written consent from CONNFLY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNFLY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.