
RJ45 Network Cable Cat.6A plug to plug with robust latch for industrial use U/UTP Slim 0.5 m white

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

Slim patch cable
The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.

With robust latch
The robust RJ45 plug is ideal for industrial applications where plugs must be plugged and unplugged frequently. Compared to conventional plugs, the industrial plug can be plugged and unplugged up to 2,000 times without the latching lug will be bent or breaking off.



Item no. 80358

EAN: 4043619803583

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x RJ45 plug
  1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- U/UTP
- RJ45 plug with robust latch
- Up to 2,000 plug and bending cycles
- Slim
- Cable gauge: 28 AWG
- Contacts gold-plated: 50 u”
- Cable diameter: ca. 3.6 mm
- Operating temperature: -20 °C ~ 60 °C
- Cable jacket material: LSZH (halogen-free)
- Colour: white
- Length: ca. 0.5 m

System requirements

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- A free RJ45 jack

Package content

- RJ45 cable

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Operating temperature:	-20 °C ~ 60 °C

Physical characteristics

Cable gauge:	28 AWG
Material:	LSZH (halogen-free)
Shielding:	U/UTP
Length:	0.5 m
Colour:	white
Cable diameter:	3.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**