

Adapter USB Type-C™ male > VGA female (DP Alt Mode)

Description

This Delock adapter is suitable for the connection of a VGA monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Item no. 63923

EAN: 4043619639236

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB Type-C™ male >
1 x VGA 15 pin female
- Chipset: Chrontel CH7212
- DisplayPort 1.3 specification
- Signal direction: USB Type-C™ input > VGA output
- Resolution up to WUXGA 1920 x 1200 @ 60 Hz
(depending on the system and the connected hardware)
- Transfer of analogue video signals
- USB bus powered
- Plug & Play
- Plastic housing with inner metal shell
- Cable length without connectors: ca. 8 cm
- Colour: black

System requirements


- Android 6.0 or above
- Chrome OS
- iPad Pro (2018)
- Mac OS 10.9.5 or above

- Windows 7/7-64/8.1/8.1-64/10/10-64
- Windows 10 Mobile
- Computer, tablet or smartphone with a free USB Type-C™ port and Displayport alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to VGA adapter

Images



General

Function:	Plug & Play
Specification:	DisplayPort 1.3
Supported operating system:	Android 6.0 or above Chrome OS Mac OS 10.9.5 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

Output:	1 x VGA 15 pin female
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Chrontel CH7212
Maximum screen resolution:	1920 x 1200 @ 60 Hz
Signal transmission:	video

Physical characteristics

Cable length:	8 cm
Connector finishing:	nickel-plated
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de