


ROCKER SWITCH MODEL: R SERIES

RATING:16(4)A 125/250V~ (cURus5)




16(4)A 250V~ T125/55 (ENEC15/CQC)

DIELECTRIC WITHSTAND VOLTAGE: 1500VAC 1 MIN

INSULATION RESISTANCE:500VDC 100MΩ (MIN)

CONTACT RESISTANCE:20mΩ INITIAL(MAX.)

ILLUMINATION: 200~250VAC



NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED: ± .012/ 0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE $\frac{1}{2}^\circ$			UNIT	mm	PART NAME	R SPEC DRAWING	DWG NO
			DRAWN BY	达志各	DESIGNED BY	蔡剑	SCALE	5/4		PART NAME		S10111A
			CHECKED BY		APPROVED BY		DATE	2024.11.21	PART NO	R-210T5W-G**A-11BNC		
2024.11.21	首次出圖	达志各										