


ST - ICT test probe

mm [inch]




ST750 PC52 X

- Minimum centers: 1.91 [.075]
- Full travel: 6.35 [.250]
- Working travel: 4.00 [.157]
- Current rating: 3-4 A
- Probe resistance: < 20m Ω
- Operating temperature: -40°C up to +120°C
- Plunger material: Steel / Gold plated
- Barrel material: Bronze / Gold plated
- Spring material: Stainless steel

Spring force at working stroke: 2.8 N [10.1 oz]

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST750 PC52 X	
	Designed	M.K.	2024.05.22	Drawing No.:	
	Drawed				
	Checked			EQUIP TEST TEST - SUPPORT - INNOVATE	
Note				A4	SHEET 1 OF 2

ST - ICT test probe



Tools for the Test Probe

Tool Handle:

TH1

Universal Insertion Bit:

TBP7500

Insertion Bit:

TBP7570

Tools for the Receptacle

Tool Handle Insertion:

TH1

Tool Handle Insertion/Extraction:

TH2

Universal Insertion Bit:

TBP7500

Insertion Bit:

TBR7535

Extraction Bit:

TBR7570

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST750 PC52 X			
	Designed	M.K.	2024.05.22	Drawing No.:			
	Drawed			EQUIPTEST TEST - SUPPORT - INNOVATE			
	Checked						
Note				A4	SHEET 2 OF 2		