



SPL (HONG KONG) LIMITED


香港九龍觀塘鴻圖道57號南洋廣場17樓1703B室
Room 1703B, 17/F., Nanyang Plaza, No.57 Hung To Road, Kwun Tong, Kowloon, HK.
Tel: 852-2342 6857 / 2342 6867 Fax: 852-2342 6847 Email: sales@spl-hk.com.hk
Website: www.buzzer.com.hk

External Drive Piezo Transducer

SPT86 series

DIMENSIONS

Date : 15 May, 2025



Ref No. : PBEE1405A



ELECTRICAL SPECIFICATIONS

Model No.	PT86-091948LMYR
Sound Pressure Level	72 dBA min. [3 Vp-p square wave, 10cm, 4800Hz in testing box]
Capacitance	12000pF $\pm$ 30% at 1000Hz
Max. Input Voltage	25 Vp-p
Heat Test	Must Be Normal [85 $\pm$ 2 $^{\circ}$ C, 24 Hours]
Cold Test	Must Be Normal [-40 $\pm$ 2 $^{\circ}$ C, 24 Hours]
Humidity Test	40 $\pm$ 2 $^{\circ}$ C, 90 ~ 95% R.H. 24 Hours
Operating Temperature	[$^{\circ}$ C] -40 ~ +85
Storage Temperature	[$^{\circ}$ C] -40 ~ +85
Terminal	SMD
Housing Material	LCP
Colour	Black
Weight	[gm] Approx. 0.2