


WiFi 6 MIMO Antenna 2 x N jack 8 dBi directional pole mounting outdoor

Description

This WLAN antenna by Delock is used for transmitting and receiving signals in accordance with IEEE 802.11 ax/ac/a/h/b/g/n outdoor.



Item no. 90705

EAN: 4043619907052

Country of origin: China

Package: Box

Technical details

- Connector: 2 x N jack
- Frequency range:
2.400 - 2.500 GHz
5.150 - 5.875 GHz
- Antenna gain: 8 dBi
- Impedance: 50 Ohm
- ~~MSMVB~~ Horizontal beam angle: 40°
- Vertical beam angle: 38°
- Operating temperature: -40 °C ~ 55 °C
- Housing material: ABS
- Housing colour: white
- Protection class: IP65
- Pole diameter: ca. 35 - 50 mm
- Dimensions (LxWxH): ca. 217 x 173 x 25 mm


System requirements

- Device with free N connectors

Package content

- WLAN antenna
- Pole mounting kit

Images



General

Mounting type:	pole
Protection class:	IP65
Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector 1:	1 x N female
Connector 2:	1 x N female

Technical characteristics

Frequency range:	5150 - 5875 MHz 2400 - 2500 MHz
Antenna gain:	8 dBi
Beam width horizontal:	40 °
Beam width vertical:	38 °
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 55° C
Humidity:	< 95 %
Polarisation:	vertical
Transmission power:	max. 150 W
VSWR:	< 2.0

Physical characteristics

Antenna type:	directional
Housing colour:	white
Weight:	574 g
Length:	217 mm

Width:	173 mm
Height:	25 mm
Maximum wind speed:	36.9 m/s

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

