




Accessories package	
Silicon o-ring	Hex nuts
	
Accessories are not locked when shipped	




Panel Cutout Ø19 mm
(Panel thickness : 14 mm MAX)

Rating: 6A 125/250V~μ 5E4 (cURus/ENEC15)
6A 3~48VDC μ 3E4 (cURus/ENEC15)

Contact Resistance: 50mΩ (max.) initial
 Insulation Resistance: 100M Ω (min)
 Dielectric Strength: 500VAC for 1 minute
 Mechanical Life: 1,000,000 cycles
 Operation Force: 350g ± 150g
 Total Travel: 3.2mm (max)
 Protection Level: IP68, IK10 (Above the panel)
 Shell Material: Aluminum Oxidation
 LED Voltage: 12 VDC (WHITE)

PK-19Z11FEW3AS-ABTN



Laser engraving

CANAL PK Series 6A 125/250V~μ 5E4 **CR**[®]US  15 12V/W

NOTE: TELEGRAPH CASES IN SETS OTHER THAN SPECIFIED 0.5 (0.5) mm).

REVISION	DESCRIPTION	REVISED BY	TOLERANCES			ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	SPEC DRAWING	DWG NO
			DRAWN BY	蔡宁燕	DESIGNED BY	蔡剑	SCALE	SCALE				PART NO
			CHECKED BY		APPROVED BY		DATE	2024.06.24				
 2024.06.24	首次出图	蔡宁燕										