

Spring plunger FSTE M3-IG 5 VG

Part no.:10.01.02.00614

<https://www.schmalz.com/10.01.02.00614>



Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Spring plunger > Spring Plungers FSTE > FSTE M3-IG 5 VG

Spring plunger with damping and height compensation




Suction cup connection: M3-F

Vacuum connection: M3-F

Spring stroke Z: 5 mm

Shape: With rotation lock

Design Data



Attribute	Value
-----------	-------

G1	M3-IG
----	-------

G2	M3-F
----	------

G3	M6x0.75-M
----	-----------

H	33.5 mm
---	---------

H2	15 mm
----	-------

LG1	3.8 mm
-----	--------

LG2	6 mm
-----	------

LG3	10 mm
-----	-------

SW1	10 mm
-----	-------

SW2	4.5 mm
-----	--------

SW3	7 mm
-----	------

Z (Stroke)	5 mm
------------	------

Spring plunger

FSTE M3-IG 5 VG

Part no.:10.01.02.00614

<https://www.schmalz.com/10.01.02.00614>



Technical Data

Attribute	Value
Spring rate	0.596 N/mm
Spring pretension	1.49 N
Spring force, center	2.98 N
Vertical load	550 N
Horizontal load	47 N
Weight	9 g
Operating temperature	0 ... 80 °C

Note: Spring force: Referred to 50% of operating stroke Static loading: Maximum static loading
Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

Spare Parts



DRUCK-FED 0.4x5 10.5 0.596

Part no.20.08.02.00093

Pressure spring

Wire size: 0.4 mm

Diameter: 5 mm

Length L: 10.5 mm

Spring rate: 0.596 N/mm