


F																																																																																															
E																																																																																															
D																																																																																															
C																																																																																															
B																																																																																															
A																																																																																															
Recommned MSAS-04PMMR-EE0003 PCB Layout																																																																																															
Recommended PCB Layout PCB Thickness 1.0mm Recommended PCB Layout PCB Thickness 1.6mm Recommended PCB Layout PCB Thickness 2.0mm																																																																																															
<table><tr><td colspan="2">UNIT:mm</td><td colspan="2">TITLE</td><td colspan="2">Amphenol LTW</td><td colspan="2">ITEM NO</td><td colspan="2">DRAWN BY</td><td colspan="2">DATE</td></tr><tr><td colspan="2">TOLERANCE</td><td colspan="2">N SEN, MI2 A-SHLD, NONE</td><td colspan="2" rowspan="3">安費諾亮泰企業股份有限公司</td><td colspan="2">MSAS-XXPMMR-EE0003</td><td colspan="2">Arvin Chan</td><td colspan="2">2025-06-18</td></tr><tr><td colspan="2">.X</td><td colspan="4">RECEPTACLE, M, M, PCB R</td><td colspan="2">CUSTOMER</td><td colspan="2">Fisher Wang</td><td colspan="2">2025-06-18</td></tr><tr><td colspan="2">.XX</td><td colspan="4">SCALE</td><td colspan="2">ALTW</td><td colspan="2">APPROVED BY</td><td colspan="2">2025-06-18</td></tr><tr><td colspan="2">.XXX</td><td colspan="2">2:1</td><td colspan="2">A4</td><td colspan="2"></td><td colspan="2">Fred Lee</td><td colspan="2"></td></tr><tr><td colspan="2">ANGLES</td><td colspan="2">A</td><td colspan="2">WC-REV.</td><td colspan="2">QC:Inspection item</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">.0</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr></table>												UNIT:mm		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE		TOLERANCE		N SEN, MI2 A-SHLD, NONE		安費諾亮泰企業股份有限公司		MSAS-XXPMMR-EE0003		Arvin Chan		2025-06-18		.X		RECEPTACLE, M, M, PCB R				CUSTOMER		Fisher Wang		2025-06-18		.XX		SCALE				ALTW		APPROVED BY		2025-06-18		.XXX		2:1		A4				Fred Lee				ANGLES		A		WC-REV.		QC:Inspection item										.0							
UNIT:mm		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE																																																																																					
TOLERANCE		N SEN, MI2 A-SHLD, NONE		安費諾亮泰企業股份有限公司		MSAS-XXPMMR-EE0003		Arvin Chan		2025-06-18																																																																																					
.X		RECEPTACLE, M, M, PCB R				CUSTOMER		Fisher Wang		2025-06-18																																																																																					
.XX		SCALE				ALTW		APPROVED BY		2025-06-18																																																																																					
.XXX		2:1		A4				Fred Lee																																																																																							
ANGLES		A		WC-REV.		QC:Inspection item																																																																																									
				.0																																																																																											
8 W1014-03-RW01A2																																																																																															


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


Recommned MSAS-05PMMR-EE0003 PCB Layout



Recommended PCB Layout
PCB Thickness 1.0mm




Recommended PCB Layout
PCB Thickness 1.6mm



Recommended PCB Layout
PCB Thickness 2.0mm

UNIT:mm



TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE

N SEN, M12 A-SHLD, NONE
RECEPTACLE, M, M, PCB R

SCALE 2:1

SIZE A4

SHEET 3 OF 4

REV. A

WC-REV. .0

QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CUSTOMER

ALTW

DRAWN BY

Arvin Chan

CHECKED BY

Fisher Wang

APPROVED BY

Fred Lee

DATE




2025-06-18

DATE

2025-06-18

DATE

2025-06-18



Wide Cover Tape Around
Out Periphery 1 Turn


Peeling Strength 0.1~1.3N Max.
(300±10mm/min)
Peeling Angle 165~180°

250PCS/Reel
With Product Charge


15PCS/Reel
With Empty
Compartment

Note:
* Connector Orientation Follow Drawing

250PCS(Connector)/Tape&Reel,
Put in a Box
4PCS BOX(1000PCS)
Put in a Carton



UNIT:mm



TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE
N SEN, M12 A-SHLD, NONE
RECEPTACLE, M, M, PCB R

SCALE 2:1 SIZE A4 SHEET 4 OF 4

REV. A WC-REV. .0 QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Arvin Chan	DATE 2025-06-18
DWG NO MSAS-XXPMMR-EE0003	CHECKED BY Fisher Wang	DATE 2025-06-18
CUSTOMER ALTW	APPROVED BY Fred Lee	DATE 2025-06-18