




DIN 963 A

~ISO 2009

4.8

Norma ritirata



## BN 20244

## Viti a testa svasata piana

con intaglio

Acciaio 4.8

zincato con passivazione ad elevato spessore

- ~UNI 6109
- ~ČSN 021151



3D Cadenas



Tutte le misure con filettatura quasi completa  
Realizzare la sede per testa svasata secondo la norma di riferimento!

| Article# | d <sub>1</sub> | d <sub>2</sub> max. | k max. | n   | t min. | L    |
|----------|----------------|---------------------|--------|-----|--------|------|
| 3371032  | M2             | 3,8                 | 1,2    | 0,5 | 0,4    | 4    |
| 3371033  |                |                     |        |     |        | 5    |
| 3371034  |                |                     |        |     |        | 8    |
| 3371030  |                |                     |        |     |        | 10   |
| 3371031  |                |                     |        |     |        | 12   |
| 3371039  | M2,5           | 4,7                 | 1,5    | 0,6 | 0,5    | 4    |
| 3371040  |                |                     |        |     |        | 5    |
| 3371041  |                |                     |        |     |        | 6    |
| 3371042  |                |                     |        |     |        | 8    |
| 3371035  |                |                     |        |     |        | 10   |
| 3371036  |                |                     |        |     |        | 16   |
| 3371037  |                |                     |        |     |        | 20   |
| 3371051  | M3             | 5,6                 | 1,65   | 0,8 | 0,6    | 4    |
| 3371053  |                |                     |        |     |        | 5    |
| 3371054  |                |                     |        |     |        | 6    |
| 3371055  |                |                     |        |     |        | 8    |
| 3371043  |                |                     |        |     |        | 10   |
| 3371044  |                |                     |        |     |        | 12   |
| 3371045  |                |                     |        |     |        | 16   |
| 3371046  |                |                     |        |     |        | (18) |
| 3371047  |                |                     |        |     |        | 20   |
| 3371048  |                |                     |        |     |        | 25   |
| 3371049  |                |                     |        |     |        | 30   |
| 3371050  |                |                     |        |     |        | 35   |
| 3371052  |                |                     |        |     |        | 40   |
| 3371064  | M4             | 7,5                 | 2,2    | 1   | 0,8    | 5    |



| Article# | d <sub>1</sub> | d <sub>2</sub> max. | k max. | n   | t min. | L    |
|----------|----------------|---------------------|--------|-----|--------|------|
| 3371066  | M4             | 7,5                 | 2,2    | 1   | 0,8    | 6    |
| 3371068  |                |                     |        |     |        | 8    |
| 3371056  |                |                     |        |     |        | 10   |
| 3371057  |                |                     |        |     |        | 12   |
| 3371058  |                |                     |        |     |        | (14) |
| 3371059  |                |                     |        |     |        | 16   |
| 3371060  |                |                     |        |     |        | 20   |
| 3371061  |                |                     |        |     |        | 25   |
| 3371062  |                |                     |        |     |        | 30   |
| 3371063  |                |                     |        |     |        | 40   |
| 3371065  |                |                     |        |     |        | 50   |
| 3371067  |                |                     |        |     |        | 60   |
| 3371077  | M5             | 9,2                 | 2,5    | 1,2 | 1      | 6    |
| 3371079  |                |                     |        |     |        | 8    |
| 3371069  |                |                     |        |     |        | 10   |
| 3371070  |                |                     |        |     |        | 12   |
| 3371071  |                |                     |        |     |        | 16   |
| 3371072  |                |                     |        |     |        | 20   |
| 3371073  |                |                     |        |     |        | 25   |
| 3371074  |                |                     |        |     |        | 30   |
| 3371075  |                |                     |        |     |        | 35   |
| 3371076  |                |                     |        |     |        | 40   |
| 3371078  |                |                     |        |     |        | 60   |
| 3371089  | M6             | 11                  | 3      | 1,6 | 1,2    | 8    |
| 3371080  |                |                     |        |     |        | 10   |
| 3371081  |                |                     |        |     |        | 12   |
| 3371082  |                |                     |        |     |        | 16   |
| 3371083  |                |                     |        |     |        | 20   |
| 3371084  |                |                     |        |     |        | 25   |
| 3371085  |                |                     |        |     |        | 30   |
| 3371086  |                |                     |        |     |        | 35   |
| 3371087  |                |                     |        |     |        | 40   |
| 3371088  |                |                     |        |     |        | 50   |
| 3371090  | M8             | 14,5                | 4      | 2   | 1,6    | 12   |
| 3371091  |                |                     |        |     |        | 16   |
| 3371092  |                |                     |        |     |        | 20   |
| 3371093  |                |                     |        |     |        | 25   |
| 3371094  |                |                     |        |     |        | 30   |
| 3371095  |                |                     |        |     |        | 35   |
| 3371096  |                |                     |        |     |        | 50   |
| 3371097  |                |                     |        |     |        | 60   |

| Article# | d <sub>1</sub> | d <sub>2</sub> max. | k max. | n   | t min. | L  |
|----------|----------------|---------------------|--------|-----|--------|----|
| 3371026  | M10            | 18                  | 5      | 2,5 | 2      | 20 |
| 3371027  |                |                     |        |     |        | 30 |
| 3371028  |                |                     |        |     |        | 40 |
| 3371029  |                |                     |        |     |        | 60 |