




Mark:

Item 1: Heat shrinkable sleeve, transparent, radiation cross-linked modified polyolefin.

Item 2: Solder rings with flux.

Item 3: Melttable rings.

ITEM	TOLERANCE	$L \pm 2.0$	$D \text{ Min}$	Qty Item 2	Color Item 3	Wire Dimensions						
						$\phi B \text{ Min}$	$\phi B \text{ Min}$ $\phi C \text{ Max}$	$\phi C \text{ Min}$				
SIZE		40.0	6.0	1	Yellow	2.8	6.0	2.8				

TERMINAL MATERIALS			UNIT: mm
Metal THICKNESS		WIRE RANGE	12-10 AWG 4-6mm ²
INSULATION MATERIALS	Polyolefin	OPERATING TEMPERATURE AND VOLTAGE	-55~125°C 600 VOLTS MAX.
		MAXIMUM ELECTRICAL RATING	48A