

# Flat electrician`s screwdriver TBI

602TBI



## Profiles




## Standards

DIN ISO 2380-1:2006 and DIN ISO 2380-2:2006

## Product features

- blade: premium hard chrome vanadium steel, entirely hardened and tempered
- blade chrome plated, black anodised tip
- handle: ergonomic shape
- three component material
- hanging hole




|  | axb       | C   | L   | D   |  |
|------------------------------------------------------------------------------------|-----------|-----|-----|-----|---------------------------------------------------------------------------------------|
| 612797                                                                             | 0.4 x 2.5 | 60  | 145 | 2.5 | 33                                                                                    |
| 612798                                                                             | 0.4 x 2.5 | 75  | 160 | 2.5 | 33                                                                                    |
| 611684                                                                             | 0.5 x 3.0 | 100 | 185 | 3   | 37                                                                                    |

|  | axb       | C   | L   | D   |  |
|--------------------------------------------------------------------------------|-----------|-----|-----|-----|-----------------------------------------------------------------------------------|
| 612799                                                                         | 0.5 x 3.0 | 150 | 235 | 3   | 39                                                                                |
| 612800                                                                         | 0.6 x 3.5 | 100 | 185 | 3.5 | 39                                                                                |
| 612801                                                                         | 0.8 x 4.0 | 100 | 185 | 4   | 43                                                                                |
| 611685                                                                         | 0.8 x 4.0 | 125 | 210 | 4   | 45                                                                                |
| 612802                                                                         | 0.8 x 4.0 | 150 | 235 | 4   | 48                                                                                |
| 612803                                                                         | 0.8 x 4.0 | 250 | 335 | 4   | 56                                                                                |
| 612804                                                                         | 1.0 x 5.5 | 125 | 225 | 5.5 | 75                                                                                |
| 611686                                                                         | 1.0 x 5.5 | 150 | 250 | 5.5 | 81                                                                                |
| 616843                                                                         | 1.0 x 5.5 | 280 | 380 | 5.5 | 103                                                                               |
| 612805                                                                         | 1.2 x 6.5 | 150 | 260 | 6.5 | 113                                                                               |
| 616844                                                                         | 1.2 x 6.5 | 280 | 390 | 6.5 | 145                                                                               |
| 612806                                                                         | 1.2 x 8.0 | 175 | 295 | 8   | 163                                                                               |

\* Images of products are symbolic. All dimensions are in mm, and weight in grams. All listed dimensions may vary in tolerance.

## Usage (pictures)



## Safety tips



- Use a screw holding screwdriver to get screws started in awkward, hard-to-reach areas.
- Use a stubby screwdriver in close quarters where a conventional screwdriver cannot be used.
- A rounded tip should be redressed with a file; make sure edges are straight.
- Screwdrivers used in the shop are best stored in a rack. This way, the proper selection of the



- Don't use pliers on the handle of a screwdriver to get extra turning power. A wrench should only be used on the square shank or bolster of a screwdriver that is especially designed for that purpose.
- Don't expose a screwdriver blade to excessive heat as it may reduce the hardness of the blade.
- Don't use a screwdriver with a split or broken handle.

right screwdriver can be quickly made.

- Keep the screwdriver handle clean; a greasy handle is apt to cause accidents.
- A screwdriver should never be used as pry bar. If it is overstressed in this manner, the blade might break and send a particle of steel into the operator's arm or even towards his eyes.

- Don't use a regular screwdriver to check a storage battery or to determine if an electrical circuit is live.

## Safety (pictures)

