



BETA 42AS

combination wrenches, open and offset ring ends



Features

Beta 42AS combination wrench in inch version: the favourite among professionals

Speed and accessibility

The 15° inclination of the fork with respect to the axis reduces the angle of recovery, while the reduced thickness of the wrench improves accessibility, even in tight spaces.

Resistance and protection

This wrench is designed for high strength: even in the event of incorrect use, it does not break suddenly, but deforms gradually, preventing sudden damage. The chrome-plated nickel finish also offers long-term protection against external influences, successfully passing the rigorous adhesion tests laid down in ISO 2819.

Homogeneity

The forging starts from a semi-finished product with a round cross-section that guarantees the fibres a homogeneous distribution, excluding the formation of dangerous internal tensions

Ergonomics

The polygonal eye is inclined by 15° to ensure greater protection of the hand during use. The shape is made directly from a mould, without additional bending. In addition, the wrench length, which is longer than that of most competitors, allows high torques to be applied with less effort.



High performance

Designed for strength, the wrench gradually deforms in the event of improper use, preventing sudden breakage.



Ergonomic design


Elegant and sleek design, characterised by light lines and a lighter feel



Compatibility

The shape is perfectly compatible with all historic wrench 42 housings and modules

Dimensions



Coded items

	Art.	MI "	MI1 "	L mm	H mm	Ø mm	S mm	S1 mm	α °	g
000421106	42AS 1/4	1/4	1/4	95	15,2	10,4	5,2	3,4	15	12
000421107	42AS 9/32	9/32	9/32	106	17,1	11,1	5,7	3,6	15	18
000421108	42AS 5/16	5/16	5/16	116	19	12,6	6,2	3,9	15	23
000421110	42AS 3/8	3/8	3/8	137	22,8	15,4	7,1	4,5	15	35
000421111	42AS 7/16	7/16	7/16	148	24,8	16,8	7,5	4,8	15	44
000421113	42AS 1/2	1/2	1/2	169	28,8	19,6	8,4	5,4	15	66
000421114	42AS 9/16	9/16	9/16	180	30,8	21	8,8	5,7	15	80
000421115	42AS 19/32	19/32	19/32	191	32,7	22,4	9,2	6,0	15	95
000421116	42AS 5/8	5/8	5/8	201	34,6	23,8	9,7	6,3	15	105
000421117	42AS 11/16	11/16	11/16	212	36,6	25,2	10,2	6,7	15	120
000421119	42AS 3/4	3/4	3/4	233	40,5	28	11,4	7,3	15	160
000421121	42AS 13/16	13/16	13/16	254	44,5	30,7	12,4	7,9	15	205
000421122	42AS 7/8	7/8	7/8	264	46,4	32,2	12,8	8,1	15	225
000421124	42AS 15/16	15/16	15/16	285	50,3	34,9	13,5	8,5	15	290
000421125	42AS 1	1	1	296	52,3	36,2	13,8	8,7	15	310
000421127	42AS 1.1/16	1.1/16	1.1/16	317	56,2	39	14,6	9,1	15	375
000421129	42AS 1.1/8	1.1/8	1.1/8	338	60,2	41,9	15,3	9,5	15	450
000421132	42AS 1.1/4	1.1/4	1.1/4	370	66	45,7	16,2	10,1	15	565
000421133	42AS 1.5/16	1.5/16	1.5/16	391	70	48,5	16,8	10,5	15	680
000421135	42AS 1.3/8	1.3/8	1.3/8	412	73,9	51,3	17,5	10,7	15	835
000421136	42AS 1.7/16	1.7/16	1.7/16	412	73,9	51,3	17,5	10,9	15	825
000421138	42AS 1.1/2	1.1/2	1.1/2	433	77,9	54	18,2	11,3	15	965

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

