

N-Channel Enhancement Mode MOSFET


Primary characteristics			
Symbol	Parameter	Value	Unit
I_D	Continuous drain current (@ $T_C=25^{\circ}\text{C}$)	10	A
V_{DS}	Drain source voltage	60	V
$R_{DS(on)}$ typ(@ $V_{GS}=10\text{V}$)	Static drain-source on-resistance	<36 Typ. 28	m Ω

Features

- **SOT-223** case for easy automatic insertion
- Pb-free and **RoHS** compliant

Application

- LED lamp
- Load switch
- Uninterruptible power supply

Case dimensions											
											
SOT-223											
Unit	A	A2	b	c	D	D1	E	e	e1	L	θ
mm	1.66 ± 0.14	1.6 ± 0.1	0.74 ± 0.08	0.30 ± 0.05	6.3 ± 0.1	3.0 ± 0.1	3.5 ± 0.2	2.3 (BSC)	4.6 ± 0.1	1.0 +0.15 -0.10	5° ± 5

Maximum ratings ($T_C = 25^{\circ}\text{C}$)			
Characteristics	Symbol	Value	Unit
Drain-source voltage	V_{DS}	60	V
Gate-source voltage	V_{GS}	± 20	V
Continuous drain current, $V_{GS} @ 10\text{V}^1$ @ $T_C=25^{\circ}\text{C}$	I_D	10	A
Continuous drain current, $V_{GS} @ 10\text{V}^1$ @ $T_C=100^{\circ}\text{C}$	I_D	8	A
Pulsed drain current	I_{DM}	30	A
Single pulse avalanche energy	E_{AS}	22	mJ
Power Dissipation @ $T_C=25^{\circ}\text{C}$	P_D	31.3	W
Operating junction temperature range	T_J, T_{STG}	-55 ~ 175	$^{\circ}\text{C}$
Thermal resistance junction-ambient ¹	$R_{\theta JA}$	60	$^{\circ}\text{C/W}$
Thermal resistance junction-case ¹	$R_{\theta JC}$	4	$^{\circ}\text{C/W}$


Maximum ratings (T _c = 25°C)						
Characteristics	Test condition	Symbol	Value			Unit
			Min.	Typ.	Max.	
Drain-source breakdown voltage	V _{GS} =0V, I _D =250μA	BV _{DSS}	60	65	-	V
BVDSS temperature coefficient	Reference to 25°C, I _D =1mA	ΔBV _{DSS} /ΔT _J	-	0.044	-	V/°C
Static drain-source on-resistance ²	V _{GS} =10V, I _D =15A	R _{DS(ON)}	-	28	36	mΩ
	V _{GS} =4.5V, I _D =7A		-	38	45	
Gate-threshold voltage	V _{DS} =V _{GS} , I _D =250μA	V _{GS(th)}	1.2	1.6	2.5	V
V _{GS(th)} temperature coefficient		ΔV _{GS(th)}	-	-4.8	-	mV/°C
Drain-source leakage current	V _{DS} =48V, V _{GS} =0V, T _J =25°C	I _{DSS}	-	-	1	μA
	V _{DS} =48V, V _{GS} =0V, T _J =55°C		-	-	5	
Gate-source leakage current	V _{GS} =±20V, V _{DS} =0V	I _{GSS}	-	-	±100	nA
Forward transconductance	V _{DS} =5V, I _D =15A	g _{FS}	-	25.3	-	S
Gate resistance	V _{DS} =0V, V _{GS} =0V, f=1MHz	R _g	-	2.5	-	Ω
Total gate charge (10V)	V _{DS} =48V V _{GS} =10V I _D =15A	Q _g	-	19	-	nC
Gate-source charge		Q _{gs}	-	2.5	-	
Gate-drain charge		Q _{gd}	-	5	-	
Turn-on delay time	V _{DD} =30V V _{GS} =10V R _G =3.3Ω I _D =15A	T _{d(on)}	-	2.8	-	ns
Rise time		T _r	-	16.6	-	
Turn-off delay time		t _{d(OFF)}	-	21.2	-	
Fall time		t _f	-	5.6	-	
Input capacitance	V _{DS} =15V V _{GS} =0V f=1.0MHz	C _{iss}	-	1027	-	pF
Output capacitance		C _{oss}	-	65	-	
Reverse transfer capacitance		C _{rss}	-	46	-	
Continuous source current ^{1, 6}	V _G =V _D =0V, force current	I _S	-	-	20	A
Pulsed source current ^{2, 6}		I _{SM}	-	-	40	A
Diode forward voltage ²	V _{GS} =0V, I _S =1A, T _J =25°C	V _{SD}	-	-	1.2	V
Reverse recovery time	I _F =15A, dI/dt=100A/μs, T _J =25°C	t _{rr}	-	12.2	-	ns
Reverse recovery charge		Q _{rr}	-	7.3	-	nC

Note :


1. The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper.
2. The data tested by pulsed, pulse width. The EAS data shows max. rating.
3. The test cond. ≤ 300μs duty cycle ≤ 2%, duty cycle is T_J = 25°C, V_{DD} = 48V, V_G = 10V, R_G = 25Ω, L = 0.1mH, I_{AS} = 13A.
4. The power dissipation is limited by 175°C junction temperature.
5. The data is theoretically the same as I_D and I_{DM}, in real applications, should be limited by total power dissipation.

Typical characteristics


Typical output characteristics




On-resistance vs. gate-source



Forward characteristics




Gate-charge characteristics




Typical characteristics


Normalized $V_{GS(th)}$ vs. T_J




Normalized $R_{DS(on)}$ vs. T_J




Capacitance




Safe operating area




Normalized maximum transient thermal impedance




Switching time waveform



Unclamped inductive switching waveform



Ordering information			
Part Number	Package	Shipping Quantity	Dimensions
10N06MSI	SOT-223	3000 pcs / reel	---



Disclaimer

Akyga semi reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Akyga semi or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on Akyga semi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Akyga semi does not assume any liability arising out of the application or use of any product or circuit. Akyga semi products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Akyga semi. Customers using or selling Akyga semi components for use in such applications do so at their own risk and shall agree to fully indemnify Akyga semi and its subsidiaries harmless against all claims, damages and expenditures.