


ST - ICT test probe

mm [inch]




ST750 RA04 N

Minimum centers: 1.91 [.075]
Full travel: 6.35 [.250]
Working travel: 4.00 [.157]
Current rating: 3-4 A
Probe resistance: < 20mΩ
Operating temperature: -40°C up to +120°C
Plunger material: BeCu / Gold plated
Barrel material: PhBr / Gold plated
Spring material: Stainless steel

Spring force at working stroke: 2.0 N [7.2 oz]

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST750 RA04 N	
	Designed	M.K.	2024.05.17	Drawing No.:	
	Drawed				
	Checked				
Note					A4
			SHEET 1 OF 2		

ST - ICT test probe



Tools for the Test Probe

- Tool Handle:
- TH1
- Universal Insertion Bit:
- TBP7500
- Insertion Bit:
- TBP7570

Tools for the Receptacle

- Tool Handle Insertion:
- TH1
- Tool Handle Insertion/Extraction:
- TH2
- Universal Insertion Bit:
- TBP7500
- Insertion Bit:
- TBR7535
- Extraction Bit:
- TBR7570

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST750 RA04 N			
	Designed	M.K.	2024.05.17	Drawing No.:			
	Drawn						
	Checked						
Note					A4	SHEET 2 OF 2	EQUIPTEST TEST - SUPPORT - INNOVATE