



嘉尼企業股份有限公司 CANAL ELECTRONIC CO.,LTD.



SPECIFICATION MODEL : TB SERIES

Electrical Life Life :10,000 cycles (cURus/ENEC15)

Mechanical Life: 50,000 cycles

Contact resistance: 20mΩ Initial (MAX),


Insulation resistance: 500VDC - 100MΩ (MIN).

Dielectric Strength:




(1) 1500VAC For 1 minute (Terminal to Enclosure)

(2) 500VAC For 1 minute (Terminal to Terminal)

Rating & ingress protection:reference to table



SWITCH FUNCTION	
	
(ON)	ON
(1-2)	2-3
(4-5)	5-6



#	Rating	IP
A	16(8)A 125/250~ T55	68
B	20(8)A 125/250~ T55	68
C	16A 6~30VDC T55	68
D	20A 6~30VDC T55	68
1	16(8)A 125/250~ T125/55	40
2	20(8)A 125/250~ T125/55	40
3	16A 6~30VDC T125/55	40
4	20A 6~30VDC T125/55	40

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED : $\pm \begin{matrix} .02 \\ 0.5 \end{matrix}$ (mm).

REVISION	DESCRIPTION	REVISED BY	TOLERANCES X.X:		ANGLE $\frac{1}{2}$			UNIT	mm	PART NAME	SPEC DRAWING	DWG NO
			DRAWN BY	范修鎔	DESIGNED BY	范修鎔	SCALE	1/1				PART NO
			CHECKED BY	ERIC	APPROVED BY		DATE	2022.12.15				
2022.12.15	首次出圖	范修鎔										