

3G-SDI Splitter 1 in > 4 out

Description

This SDI splitter by Delock can be used to receive signals of one SDI input source, such as a DVR, an HD-SDI camera or other SDI device, to up to 4 different output devices such as SDI monitors.



Item no. 93250

EAN: 4043619932504

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - Input:
 - 1 x BNC female (3G-SDI)
 - 1 x 5 V DC jack
 - Output:
 - 4 x BNC female (3G-SDI)
- Supported resolution:
 - SD 480i, 525i and 625i
 - HD 720p 24, 25, 30, 50 and 60 Hz
 - HD 1080i 50, 60 Hz
 - HD 1080p 24, 25, 30, 50 and 60 Hz
- Robust metal housing
- Power consumption: max. 1.2 W
- Dimensions (LxWxH): ca. 162 x 82 x 25 mm

Power supply specification


- Power supply type: Euro wall power plug
- Model identifier: FJ-SW1160501000DE
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.3 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W

- Average active efficiency: 75.7 %
- No-load power consumption: 0.07 W
- DC power connector: 5.5 x 2.1 mm
- Power supply cable length: ca. 1.5 m
- Ground outside, plus inside

Package content

- 3G-SDI splitter
- 4 x rubber feet
- Power supply

Images



Interface

Output:	4 x BNC female
Input:	1 x 5 V DC female 5,5 mm x 2,1 mm 1 x BNC female

Technical characteristics

Maximum screen resolution:	1920 x 1080 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	metal
Length:	162 mm
Width:	82 mm
Height:	25 mm
Colour:	black

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.3 A
Power supply output:	5.0 V / 1.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de