


NL-203AA GNSS GALILEO GPS High Gain Antenna with SMA plug 5 m outdoor

Description

This GNSS antenna by Navilock can be used with an existing GNSS receiver with SMA connection. Improvement of reception will be provided by placing the antenna, e.g. on the hat rack or car roof, where it has a better or free view to the sky. The antenna is waterproof and can temporary also be used outside of the vehicle.



Item no. 60650

EAN: 4043619606504

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: 1 x SMA plug
- Connector finishing: brass gold plated
- External active additional antenna for GNSS receiver
- **Internal patch antenna:**
 - Antenna gain: 5 dBic
 - Bandwidth: > 20 MHz
 - VSWR: 2.0
 - Polarisation: RHCP
 - Dimensions (LxWxH): ca. 25 x 25 x 4 mm
 - Dimension ground plate metal (LxW): ca. 40 x 40 mm (PCB)
- **LNA GNSS:**
 - Gain: 30 dB
 - VSWR: 1.5
 - Input voltage: 3.0 - 5.0 V
 - noise figure: 1.5 @ 25 °C +/- 10 °C
- Frequency range: 1575.42 MHz +/- 1.02 MHz
- Impedance: 50 Ohm
- Operating temperature: -40 °C ~ 80 °C
- Protection class: IPX6
- Magnetic bottom
- Current consumption: ca. 10 mA @ 5.0 V
- Cable type: RG-174
- Cable attenuation: 5.70 dB

- Cable length: ca. 5 m
- Dimensions (LxWxH): ca. 50.6 x 50.6 x 15.1 mm

System requirements

- Device with a free SMA jack

Package content

- GNSS antenna

Images



General

Mounting type:	magnetic
Protection class:	IPX6
Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Operating voltage:	3 V - 5 V
Frequency range:	1575.42 MHz
Bandwidth:	± 20 MHz
Antenna gain:	30 dB
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 85 °C
Polarisation:	RHCP
Noise figure:	< 1.5 dB
Current consumption:	10 mA
VSWR:	2.0

Physical characteristics

Antenna type:	patch
Length:	50.6 mm
Width:	50.6 mm
Height:	15.6 mm

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@navilock.de
Website	www.navilock.de

