

LTE Antenna SMA plug 0 - 4 dBi omnidirectional rotatable with tilt joint black

Description

This LTE antenna by Delock can be installed indoors and takes advantage of all LTE bands. It is completely compatible to GSM, UMTS, Bluetooth, WLAN 2.4 GHz, ZigBee, DECT and Z-Wave.



Item no. 88976

EAN: 4043619889761

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connector: SMA plug
- LTE band: 1-10; 12; 19; 25; 30; 33-41
- Frequency range:
 - 698 - 791 MHz
 - 824 - 960 MHz
 - 1710 - 2170 MHz
 - 2300 - 2400 MHz
 - 2500 - 2700 MHz
- Compatible to GSM, UMTS, Bluetooth, WLAN 2,4 GHz, ZigBee, DECT, Z-Wave
- Antenna gain:
 - 1.5 dBi @ 698 - 791 MHz
 - 0 dBi @ 824 - 960 MHz
 - 1.5 dBi @ 1710 - 2170 MHz
 - 4 dBi @ 2300 - 2400 MHz
 - 4 dBi @ 2500 - 2700 MHz
- Impedance: 50 Ohm
- Polarisation: linear, vertical
- VSWR: 4.0
- Operating temperature: -10 °C ~ 55 °C
- Housing material: ABS
- Colour: black
- Length:

- ca. 231.50 mm (with tilt joint)
- ca. 199.20 mm (without tilt joint)
- Diameter:
 - ca. 19.70 mm (top)
 - ca. 21.50 mm (max.)
 - ca. 13.20 mm (SMA)


System requirements

- Device with a free SMA jack

Package content

- LTE antenna

Images



Interface

Connector:	SMA Stecker
------------	-------------

Technical characteristics

Frequency range:	824 - 960 MHz 2300 - 2400 MHz 2500 - 2700 MHz 1710 - 2170 MHz 698 - 791 MHz
Gain:	1.5 dBi @ 698 - 791 MHz 0 dBi @ 824 MHz - 960 MHz 1.5 dBi @ 1710 MHz - 2170 MHz 4 dBi @ 2300 MHz - 2400 MHz 4 dBi @ 2500 - 2700 MHz
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 55 °C
Polarisation:	linear vertical
VSWR:	4.0

Physical characteristics

Housing material:	ABS
Diameter connector:	13.20 mm
Length with tilt joint:	231.50 mm
Length without tilt joint:	199.20 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

