

Antenna Cable I-PEX Inc., MHF® I plug to I-PEX Inc., MHF® I plug 1.13 30 cm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 89609

EAN: 4043619896097

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x I-PEX Inc., MHF® I plug >
 - 1 x I-PEX Inc., MHF® I plug
- Impedance: 50 Ohm
- Cable type: 1.13
- Cable: coaxial
- Cable attenuation: 3.2 dB @ 2.4 GHz per meter
- Cable diameter: ca. 1.13 mm
- Smallest bending radius: 4.5 mm
- Cable colour: black
- Cable length incl. connectors: ca. 30 cm


System requirements

- Device with two free I-PEX Inc., MHF® I connectors

Package content

- Antenna cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x I-PEX Inc., MHF® I plug
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Cable category:	coaxial
Cable type:	1.13
Cable attenuation:	3.2 dB @ 2.4 GHz per meter
Cable colour:	black
Cable length incl. connectors:	30 cm
Smallest bending radius:	4.5 mm
Cable diameter:	1.13 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

