

1932B10

reversible drill



- Sturdy and handy
- Autochuck
- Reversible lever
- Slip-proof handle
- Exhaust through handle

Free speed	1,800 rpm
Chuck capacity	1÷10 mm
Power	0,44 kW
Spindle thread	3/8" - 24UNF
Air inlet	1/4" GAS
Working pressure	6,2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	160 l/min
Weight	1,2 kg

	art.	
019320040	1932B10	1,2

