


CATALOG CARD

Quick connector 0,2-4,0 mm², 4 pins



Information	
Index	E.4192
EAN	5908793101339
Certificates and standards	
CE, PN-EN 60998-1:2006	
Link to the declaration	
https://www.pawbol.pl/wp-content/uploads/2024/02/E.20J-Szybkozlaczki-02%C3%B74mm%C2%B2.pdf	
Technical data	
Colour	Transparent with orange levers
Electrical data and parameters	
Rated insulation voltage	450V
Rated current	32A
Number of contacts	4
Working temperature	From -40°C to 85°C
Dimensions	
Height	10,8mm
Width	28,1mm
Length	19,2mm
Weight	5,6g
Installation information	
Cable stripping length	11mm
Connection type	Quick connector
Conductor cross-sections for wire	0,2mm ² - 4,0mm ²
Conductor cross-sections for tinned cable	0,2mm ² - 4,0mm ²
Conductor cross-sections for a cable fertilized with a ferrule	0,2mm ² - 2,5mm ²
Packing	
Number of pieces in the package	100

PAWBOL S.A. MANUFACTURER OF ELECTROTECHNICAL EQUIPMENT