

WLAN 802.11 b/g/n Antenna RP-SMA plug 2 dBi omnidirectional with tilt joint black

Description

This Wireless LAN antenna can be connected to a WLAN device with RP-SMA interface, in order to send and receive signals.



Item no. 88339

EAN: 4043619883394

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors: 1 x RP-SMA plug
- Frequency range: 2.400 - 2.500 GHz
- Antenna gain: 2 dBi
- Impedance: 50 Ohm
- VSWR: 2.0
- Polarisation: linear, vertical
- Operating temperature: -20 °C ~ 60 °C
- Colour: black
- Length:
 - ca. 108.00 mm (with tilt joint)
 - ca. 82.50 mm (without tilt joint)
- Diameter:
 - ca. 7.80 mm (top)
 - ca. 10.00 mm (RP-SMA)

System requirements

- Device with a free RP-SMA jack

Package content

- WLAN antenna

Images



General

Suitable for indoor:	yes
----------------------	-----

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	2400 - 2500 MHz
Antenna gain:	2 dBi
Impedance:	50 Ohm
Polarisation:	linear vertical
VSWR:	2.0

Physical characteristics

Antenna type:	omnidirectional dipol antenna
Housing material:	PC PBT
Diameter:	7.8 mm
Diameter connector:	10.0 mm
Length with tilt joint:	108.0 mm
Length without tilt joint:	82.5 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

